

ExStik[®] Waterproof Refillable pH Meter

Features flat surface electrode, RENEW and CALibration alerts, memory, and bargraph
Indicator tells you it's time to replace your electrode and eliminates guesswork

Features:

- ✓ Refillable pH electrode is easily serviced. Fresh reference solution maintains high accuracy. Eliminates concern with shelf life.
- ✓ Flat Surface Electrode measures pH in liquids, semi-solids, and solids. No more electrode breakage or clogged junctions.
- ✓ CAL alerts tells you it's time to recalibrate. Ensures accuracy.
- ✓ Memory records and recalls 15 sequentially tagged readings. Allows detection of changes over time.
- Analog bargraph displayed on LCD. Shows trends in acidity or alkalinity.
- 1, 2 or 3 point calibration automatically recognizes buffer solutions. Order pH buffers separately.
- Automatic Temperature Compensation
- Simultaneous display of pH and Temperature
- Waterproof to IP57 standard
- Display indicates when the reading is stabilized
- Data Hold, Auto power off and low battery indication
- Waterproof design floats in water and protects the meter in wet environment
- Interchangeable probes available for Chlorine & ORP
- Optional weighted base (EX006) holds plastic cup and ExStik[®] meter
- Complete with refillable flat surface pH electrode, 1.5mL bottle KCl, 2 reference junctions, 2 removal tools, protective sensor cap, sample cup with cap, four 3V CR-2032 button batteries, and 48" (1.2m) neckstrap. **Order pH buffers separately**

Ordering Information:

PH110	Waterproof Refillable ExStik [®] pH Meter
PH115	Spare Refillable pH ExStik [®] Electrode Module
PH113	Reference Refill Solution Kit for PH110
EX006	Weighted base with 5 solution cups
PH103	Tripak buffers (6ea - 4, 7, 10pH & 2 Rinse solutions)
PH105	Spare pH ExStik [®] Electrode Module
EX007	Spare sample solution cups (24pk)
CA903	Carrying case for ExStik [™] kit
RE305	Spare Probe, ORP
CL205	Spare Probe, Chlorine
EX010	Extension Cable, 3ft (1 Meter) with probe weight for ExStik
EX050	Extension Cable, 16ft (5 Meter) with probe weight for ExStik
PH115	Spare Probe, pH, Refillable Reference
PH4-P	pH 4 Buffer Solution (2 Bottles, 1 Pint (475 mL) Each
PH7-P	pH 7 Buffer Solution (2 Bottles, 1 Pint (475 mL) Each
PH10-P	pH 10 Buffer Solution (2 Bottles, 1 Pint (475 mL) Each
CA895	Carrying Case, Small with Belt Loop
EX800	ExStik 3-in-1 Kit (Chlorine, pH, Temp)
EX900	ExStik 4-in-1 Kit (Chlorine, pH, ORP, Temp)
D0610	ExStik DO/pH/Conductivity Kit



Specifications	
pH	0.00 to 14.00pH
Temperature	23 to 194°F (-5 to 90°C)
Resolution	0.01pH, 0.1°
Accuracy	±0.01pH, ±1.8°F/±1°C
Power	four LR44 button batteries
Dimensions	1.4 x 6.8 x 1.6" (35.6 x 172.7 x 40.6mm)
Weight	3.8oz (110g)

