





PART NO.	"A"
LEDS2E-3-01	3/16 (4.8)
LEDS2E-4-01	1/4 (6.5)
LEDS2E-6-01	3/8 (9.5)
LEDS2E-8-01	1/2 (12.7)
LEDS2E-10-01	5/8 (15.9)
LEDS2E-12-01	3/4 (19.1)
LEDS2E-14-01	7/8 (22.2)
LEDS2E-16-01	1 (25.4)



NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01)
FLAME RETARDANT, NYLON (RMS-19),
AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER, REPLACE "-01" WITH "-19"
2. COLOR: NATURAL.

			TITLE: LED SPACER (TYPE 2E)						DWG IN IN (MM)				
E	ADDED MAT'L NOTES		SM 06.05.02	TOLERANCES UNLESS NOTED		FILE # LEDS2E	DWN: JB	APP:		FINAL			
D	CHANGED FILE NO.		SM 02.27.02	.XX=±.010		MAT'L: SEE NOTES		DT: 1.25.96	DT:		PART # SEE TABLE	PRINT TYPE CA	
C	CORRECTED DIM .04 & .08		SM 02.13.01	.XXX=±.005		RE: RICHCO, INC.		RICHCO INC.					
B	COMPLETELY REDRAWN TO UK NEW STYLE		JK 9.10.99	FRAC=±1/64				PO BOX 804238,CHICAGO,60680					
A	ORIGINALLY DRAWN BY JB		JB 1.25.96	ANG=±1°				(773) 539-4060					
REV	DESCRIPTION		ENGR DATE										