



Application Range

Saddle clamp strain relief gland for harsh application condition for plant engineering and electric motor manufacturing.

Technical Data

Material: Body: Nickel Plated Brass
Seal: CR
O Ring: NBR

Protection Rating: IP55

Temperature Range: -20°C to +80°C

Article List

Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
1572203	Cable gland, metal, PG9	PG9	6 – 8.5	17	30	6
1572219	Cable gland, metal, PG11	PG11	8 – 12	20	30	6
1572225	Cable gland, metal, PG13.5	PG13.5	12 – 14	22	34	6.5
1572231	Cable gland, metal, PG16	PG16	13 – 16	24	35	6.5
2127775	Cable gland, metal, PG21	PG21	15 – 21	30	41	7
2127781	Cable gland, metal, PG29	PG29	20 – 29	40	46	8
4330838	Cable gland, metal, M16	M16	5 – 8	18	29	5
4330850	Cable gland, metal, M20	M20	7 – 12	22	30	6
4330866	Cable gland, metal, M20	M20	11 – 13	22	33.5	6
4330872	Cable gland, metal, M20	M20	13 – 15	24	34.5	6
4330888	Cable gland, metal, M25	M25	16 – 19.3	30	41	7