

Aluminum Capacitors

+ 85 °C, Tubular, Axial Lead, General Purpose



Fig.1 Component outlines

FEATURES

- General purpose capacitor
- Rugged construction
- Largest CV ratings in axial lead capacitor



QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case size Ø D x L in mm	0.75" x 1.125" [19.05 x 28.575] to 1.375" x 4.125" [34.925 x 104.775]
Operating temperature	- 40 °C to + 85 °C
Rated Capacitance range, C _R	15 µF to 220 000 µF
Tolerance on C _R	- 10 %, + 50 %; - 10 %, + 75 %
Rated voltage range, U _R	6.3 WVDC to 450 WVDC
Termination	axial leads
Life validation test at 85 °C	1000 hours: Δ CAP ≤ 15 % from initial measurement. Δ ESR ≤ 1.5 x initial specified limit. Δ DCL ≤ initial specified limit
Shelf life at 85 °C	500 hours: Δ CAP ≤ 10 % from initial measurement. Δ ESR ≤ 1.3 x initial specified limit. Δ DCL ≤ 2.0 x initial specified limit
DC leakage current	$I = K \sqrt{Cv}$ K = 6.0 at + 25 °C; 36.0 at + 85 °C I in µA, C in µF, V in Volts


RIPPLE CURRENT MULTIPLIERS			
TEMPERATURE			
Ambient Temperature		Multipliers	
+ 75 °C		1.4	
+ 65 °C		1.7	
+ 45 °C and below		2.0	
FREQUENCY (Hz)			
WVDC	50 - 60	300 - 400	1000 AND UP
0 - 50	0.85	1.10	1.15
51 - 299	0.85	1.15	1.20
300 - ∞	0.80	1.30	1.40

LOW TEMPERATURE PERFORMANCE	
CAPACITANCE RATIO C - 40 °C/C + 25 °C MINIMUM at 120 Hz	
Rated Voltage (WVDC)	Capacitance Remaining
0 - 40	35
41 - 63	45
64 - 100	60
101 - 350	20
351 - 450	15
ESR RATIO ESR - 40 °C/ESR + 25 °C MAXIMUM at 120 Hz	
Rated Voltage (WVDC)	Multiplier
0 - 40	60
41 - 63	55
64 - 100	65
101 - 350	180
351 - 450	190

DIMENSIONS in inches [millimeters]							
CASE CODE	STYLE 6 AND 7		TYPICAL WEIGHT	CASE CODE	STYLE 6 AND 7		TYPICAL WEIGHT
	D	L			D	L	
GE	0.760 ± 0.020 [19.3 ± 0.51]	1.141 ± 0.062 [29.0 ± 1.58]	0.46 Oz. (13 Grams)	GL	0.760 ± 0.020 [19.3 ± 0.51]	2.141 ± 0.062 [54.4 ± 1.58]	0.74 Oz. (21 Grams)
GJ	0.760 ± 0.020 [19.3 ± 0.51]	1.641 ± 0.062 [41.7 ± 1.58]	0.67 Oz. (19 Grams)	GP	0.760 ± 0.020 [19.3 ± 0.51]	2.641 ± 0.062 [67.1 ± 1.58]	0.88 Oz. (25 Grams)
GS	0.760 ± 0.020 [19.3 ± 0.51]	3.141 ± 0.062 [79.8 ± 1.58]	1.16 Oz. (33 Grams)	KS	1.135 ± 0.020 [28.8 ± 0.51]	3.141 ± 0.062 [79.8 ± 1.58]	2.54Oz. (72 Grams)
GT	0.760 ± 0.020 [19.3 ± 0.51]	3.641 ± 0.062 [92.5 ± 1.58]	1.34 Oz. (38 Grams)	KT	1.135 ± 0.020 [28.8 ± 0.51]	3.641 ± 0.062 [92.5 ± 1.58]	2.96 Oz. (84 Grams)
HE	0.885 ± 0.020 [22.5 ± 0.51]	1.141 ± 0.062 [29.0 ± 1.58]	0.63 Oz. (18 Grams)	KD	1.135 ± 0.020 [28.8 ± 0.51]	4.141 ± 0.062 [105.2 ± 1.58]	3.35 Oz. (95 Grams)
HJ	0.885 ± 0.020 [22.5 ± 0.51]	1.641 ± 0.062 [41.7 ± 1.58]	0.95 Oz. (27 Grams)	LE	1.260 ± 0.020 [32.0 ± 0.51]	1.141 ± 0.062 [29.0 ± 1.58]	1.13 Oz. (32 Grams)

DIMENSIONS in inches [millimeters]

CASE CODE	STYLE 6 AND 7		TYPICAL WEIGHT	CASE CODE	STYLE 6 AND 7		TYPICAL WEIGHT
	D	L			D	L	
HL	0.885 ± 0.020 [22.5 ± 0.51]	2.141 ± 0.062 [54.4 ± 1.58]	1.02 Oz. (29 Grams)	LJ	1.260 ± 0.020 [32.0 ± 0.51]	1.641 ± 0.062 [41.7 ± 1.58]	1.62 Oz. (46 Grams)
HP	0.885 ± 0.020 [22.5 ± 0.51]	2.641 ± 0.062 [67.1 ± 1.58]	1.38 Oz. (39 Grams)	LL	1.260 ± 0.020 [32.0 ± 0.51]	2.141 ± 0.062 [54.4 ± 1.58]	2.11 Oz. (60 Grams)
HS	0.885 ± 0.020 [22.5 ± 0.51]	3.141 ± 0.062 [79.8 ± 1.58]	1.73 Oz. (49 Grams)	LP	1.260 ± 0.020 [32.0 ± 0.51]	2.641 ± 0.062 [67.1 ± 1.58]	2.65 Oz. (75 Grams)
HT	0.885 ± 0.020 [22.5 ± 0.51]	3.641 ± 0.062 [92.5 ± 1.58]	2.08 Oz. (59 Grams)	LS	1.260 ± 0.020 [32.0 ± 0.51]	3.141 ± 0.062 [79.8 ± 1.58]	3.14 Oz. (89 Grams)
JE	1.010 ± 0.020 [25.7 ± 0.51]	1.141 ± 0.062 [29.0 ± 1.58]	0.81 Oz. (23 Grams)	LT	1.260 ± 0.020 [32.0 ± 0.51]	3.641 ± 0.062 [92.5 ± 1.58]	3.63 Oz. (103 Grams)
JJ	1.010 ± 0.020 [25.7 ± 0.51]	1.641 ± 0.062 [41.7 ± 1.58]	1.02 Oz. (29 Grams)	LD	1.260 ± 0.020 [32.0 ± 0.51]	4.141 ± 0.062 [105.2 ± 1.58]	4.16 Oz. (118 Grams)
JL	1.010 ± 0.020 [25.7 ± 0.51]	2.141 ± 0.062 [54.4 ± 1.58]	1.55 Oz. (44 Grams)	ME	1.375 ± 0.020 [34.9 ± 0.51]	1.141 ± 0.062 [29.0 ± 1.58]	1.38 Oz. (39 Grams)
JP	1.010 ± 0.020 [25.7 ± 0.51]	2.641 ± 0.062 [67.1 ± 1.58]	1.87 Oz. (53 Grams)	MJ	1.375 ± 0.020 [34.9 ± 0.51]	1.641 ± 0.062 [41.7 ± 1.58]	1.98 Oz. (56 Grams)
JS	1.010 ± 0.020 [25.7 ± 0.51]	3.141 ± 0.062 [79.8 ± 1.58]	2.22 Oz. (63 Grams)	ML	1.375 ± 0.020 [34.9 ± 0.51]	2.141 ± 0.062 [54.4 ± 1.58]	2.57 Oz. (73 Grams)
JT	1.010 ± 0.020 [25.7 ± 0.51]	3.641 ± 0.062 [92.5 ± 1.58]	2.54 Oz. (72 Grams)	MP	1.375 ± 0.020 [34.9 ± 0.51]	2.641 ± 0.062 [67.1 ± 1.58]	3.21 Oz. (91 Grams)
KE	1.135 ± 0.020 [28.8 ± 0.51]	1.141 ± 0.062 [29.0 ± 1.58]	0.92 Oz. (26 Grams)	MS	1.375 ± 0.020 [34.9 ± 0.51]	3.141 ± 0.062 [79.8 ± 1.58]	3.81 Oz. (108 Grams)
KJ	1.135 ± 0.020 [28.8 ± 0.51]	1.641 ± 0.062 [41.7 ± 1.58]	1.31 Oz. (37 Grams)	MT	1.375 ± 0.020 [34.9 ± 0.51]	3.641 ± 0.062 [92.5 ± 1.58]	4.44 Oz. (126 Grams)
KL	1.135 ± 0.020 [28.8 ± 0.51]	2.141 ± 0.062 [54.4 ± 1.58]	1.73 Oz. (49 Grams)	MD	1.375 ± 0.020 [34.9 ± 0.51]	4.141 ± 0.062 [105.2 ± 1.58]	5.04 Oz. (143 Grams)
KP	1.135 ± 0.020 [28.8 ± 0.51]	2.641 ± 0.062 [67.1 ± 1.58]	2.15 Oz. (61 Grams)	-	-	-	-

DIMENSIONS AND AVAILABLE FORMS

Aluminum Capacitors
+ 85 °C, Tubular, Axial Lead, General Purpose

Vishay Sprague

ELECTRICAL DATA

SYMBOL	DESCRIPTION
μF	rated capacitance
± %	F = 10 %, + 50 %
DC	voltage rating at 85 °C
GL	see dimensions in millimeters table
6	termination

ORDERING EXAMPLE*

Electrolytic capacitor 53D series

53D 282 G 025 GJ 6

* Note: For lead (Pb)-free / RoHS compliant products add suffix "E3" to part number

Example: 53D282G025GJ6E3

ELECTRICAL DATA AND ORDERING INFORMATION

CAPACITANCE (μF)	CASE CODE	PART NUMBER*	MAX. ESR at + 25 °C 120 Hz (Milliohms)	MAX. RMS RIPPLE at + 85 °C 120 Hz (Milliamps)
16 WVDC at + 85 °C, SURGE = 18 V				
6900.0	HJ	53D692G016HJ6	73	2150
10000.0	HL	53D103G016HL6	52	2840
25 WVDC at + 85 °C, SURGE = 35 V				
2800.0	GJ	53D282G025GJ6	103	1650
4300.0	HJ	53D432G025HJ6	72	2170
6200.0	HL	53D622G025HL6	51	2870
11000.0	JP	53D113G025JP6	33	4230
35 WVDC at + 85 °C, SURGE = 45 V				
1100.0	GE	53D112G035GE6	219	980
2100.0	GJ	53D212G035GJ6	111	1590
3200.0	HJ	53D322G035HJ6	77	2090
4700.0	HL	53D472G035HL6	54	2780
8300.0	JP	53D832G035JP6	34	4110
50 WVDC at + 85 °C, SURGE = 70 V				
1000.0	GE	53D102G050GE6	231	950
1300.0	GJ	53D132G050GJ6	131	1470
1900.0	HJ	53D192G050HJ6	94	1900
2800.0	HL	53D282G050HL6	65	2540
3800.0	JL	53D382G050JL6	51	3090
5000.0	JP	53D502G050JP6	40	3810
63 WVDC at + 85 °C, SURGE = 80 V				
1000.0	GJ	53D102G063GJ6	145	1400
2200.0	HL	53D222G063HL6	86	2210
200 WVDC at + 85 °C, SURGE = 250 V				
350.0	JL	53D351F200JL6	499	1000
460.0	JP	53D461F200JP6	379	1250
250 WVDC at + 85 °C, SURGE = 300 V				
56.0	GE	53D560F250GE6	3035	263
100.0	GJ	53D101F250GJ6	1593	420
130.0	HJ	53D131F250HJ6	1238	520
400 WVDC at + 85 °C, SURGE = 450 V				
100.0	JL	53D101F400JL6	1524	560
140.0	JS	53D141F400JS6	1084	790
150.0	JS	53D151F400JS6	1011	820

Note

* These Part Numbers are normally stocked. Many other values are available on special order. Please contact your distributor for price and delivery.



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[53D103G050JT7](#) [53D152G063HJ7](#) [53D112G035GE7](#) [53D101F250GJ6](#) [53D101F400JL6](#) [53D101F450HP6](#)
[53D102G050GE6](#) [53D103F035JP6](#) [53D103G016HL6](#) [53D113G025JP6](#) [53D131F250HJ6](#) [53D132G050GJ6](#)
[53D151F400JS6](#) [53D153F025JP6](#) [53D222G063HL6](#) [53D282G025GJ6](#) [53D282G050HL6](#) [53D332G016GE6](#)
[53D351F200JL6](#) [53D371F250JP6](#) [53D461F200JP6](#) [53D470F400HJ6](#) [53D472G035HL6](#) [53D500F250GE6](#)
[53D502G050JP6](#) [53D560F250GE6](#) [53D622G025HL6](#) [53D682G050JP6](#) [53D832G035JP6](#) [53D692G016HJ6](#)
[53D141F400JS6](#) [53D142](#) [53D479](#) [53D574](#) [53D382G050JL6](#) [53D212G035GJ6](#) [53D102G063GJ6](#) [53D103G063KD6](#)
[53D432G025HJ6](#) [53D322G035HJ6](#) [53D272G050HJ6](#) [53D112G035GE6](#) [53D192G050HJ6](#) [53D681F200JS6](#)
[53D143](#) [53D152F100JL6](#)