


Tab Contacts Asymmetric

**Tabs 4.8 x 0.8 mm
with Asymmetric
Steel Top Spring,
Mates with
Standard Power Timer**

Extraction Tool:
Part No. **726544-1**

Product Specification:
108-18064

Application Specification:
114-18052



Standard Tab Contacts

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers				
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *
0.2-0.5	-	1.1-1.6	-1 / -2	963824	3,000	963825	500	x-878609-x
0.5-1.0	-	1.4-2.0	-1 / -2	962903	3,000	963816	500	x-878610-x
0.5-1.0	2.0-2.7	-	-1 / -2	962908	2,000	963821	500	x-878612-x
> 1.0-2.5	-	2.1-2.9	-1 / -2	962904	2,500	963817	500	x-878611-x
> 2.5-4.0	3.3-4.5	-	-1 / -2	962910	1,700	963823	500	x-878614-x

Tab Contacts with Single Wire Sealing System

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers				
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *
0.5-1.0	-	6.0	-1 / -2	962905	1,000	963818	1,200	x-878852-x
> 1.0-2.5	-	6.0	-1 / -2	962906	1,000	963819	500	x-878853-x
> 2.5-4.0	-	6.0	-1 / -2	962907	1,000	963820	500	x-878854-x

*) **Material and Finish:**
xxx-1 = CuSn, pre-tin plated
xxx-2 = CuFe, pre-tin plated

*) The pre- and suffix for the applicators depends on the applied termination equipment.