



FEATURES:

- BNC connector and breakout wires are molded directly to the cable for added pull strength.
- Alligators clip jaws open up to .187" (4.75mm)
- Schematic: Black alligator to BNC shell, red alligator to BNC center contact.
- BNC features PTFE dielectric and gold plated center contact for optimum electrical performance.

MATERIALS:

BNC: Body: Brass, Nickel Plated, Center Pin: Brass, Gold Plated, Impedance: 50 Ohms

Strain Relief and Molded Breakout: PVC, Color: Black

Receptacle: Body – Phosphor Bronze, Housing: Polypropylene, Color: One Black, One Red

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 500VRMS Max.

Operating Temperature: 50°C (+122°F) Max.

ORDERING INFORMATION: Model 4945-K-XX

XX = Length in inches. Std. Lengths: 18" (45.72cm), 24" (60.96 cm), 36" (91.44 cm), 48" (121.92 cm) & 60" (152.40 cm). Additional lengths can be quoted upon request.

Ordering Example: 4945-K-36, Cable length will be 36" (9.44 mm) long.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4945-K-60](#) [4945-K-18](#) [4945-K-48](#) [4945-K-24](#) [4945-K-36](#)