




Wiha Box Wrenches

475 Box Wrenches Metric DIN 838 / ISO 10104



Satin chromed sure grip body. Made from 31CRV3 high performance forged tool steel. Precision formed for an exact fit. 12 point drive.

Item			OAL	OAL	H ¹	H ²	D ¹	D ²		
No.	mm	mm	mm	Inch	mm	mm	mm	mm	lbs.	pkg.
475 01	5.5 x	7.0	165	6.5	5.8	6.3	10.6	12.2	.09	10
475 02	6.0 x	7.0	165	6.5	5.8	6.3	10.6	12.2	.09	10
475 41	7.0 x	8.0	170	6.7	6.0	6.7	12.2	13.5	.12	10
475 03	8.0 x	9.0	180	7.1	6.7	7.3	13.7	15.1	.13	10
475 04	10.0 x	11.0	195	7.6	7.5	8.1	16.4	17.9	.19	10
475 05	12.0 x	13.0	216	8.5	8.4	9.0	19.7	20.9	.26	10
475 06	14.0 x	15.0	238	9.3	9.6	10.1	22.4	25.0	.33	10
475 07	16.0 x	17.0	262	10.3	10.2	10.4	25.4	27.0	.44	10
475 08	18.0 x	19.0	290	11.4	10.8	11.0	27.8	29.7	.55	1
475 09	20.0 x	22.0	320	12.5	11.5	12.2	31.8	34.0	.75	1
475 10	21.0 x	23.0	326	12.8	11.8	12.5	32.4	35.3	.77	1
475 11	24.0 x	26.0	337	13.2	12.8	13.9	37.0	41.0	.92	1
475 12	25.0 x	28.0	346	13.6	13.0	14.2	29.2	43.0	1.1	1
475 13	27.0 x	29.0	346	13.6	13.9	14.6	40.5	45.3	1.1	1
475 14	30.0 x	32.0	360	14.1	13.9	15.5	45.5	49.0	1.3	1
475 15	30.0 x	34.0	380	14.9	14.8	16.5	45.5	51.8	1.3	1
475 16	36.0 x	41.0	440	17.3	18.0	19.5	53.5	60.5	2.5	1
475 17	46.0 x	50.0	500	19.6	21.4	22.4	67.0	73.0	3.6	1

475 Box Wrenches Inch DIN 838 / ISO 10104

Satin chromed sure grip body. Made from 31CRV3 high performance forged tool steel. Precision formed for an exact fit. 12 point drive.

Item	 AF	OAL	OAL	H ¹	H ²	D ¹	D ²			
No.	Inch	Inch	mm	Inch	mm	mm	mm	lbs.	pkg.	
475 18	1/4x5/16		170	6.7	6.0	6.7	12.2	13.5	.12	10
475 19	5/16x3/8		180	7.1	6.7	7.5	13.7	16.4	.14	10
475 20	3/8x7/16		195	7.6	7.5	8.1	16.4	17.9	.19	10
475 21	7/16x1/2		216	8.5	8.4	9.0	18.3	20.9	.24	10
475 22	1/2x9/16		239	9.4	9.0	9.3	20.9	22.3	.32	10
475 23	9/16x5/8		239	9.4	9.3	9.7	22.3	25.0	.32	10
475 24	5/8x11/16		262	10.3	10.2	10.4	25.4	27.0	.42	10
475 25	5/8x3/4		290	11.4	10.2	11.0	25.4	29.7	.51	10
475 26	11/16x3/4		290	11.4	10.8	11.0	27.8	29.7	.58	1
475 27	3/4x25/32		290	11.4	11.0	11.4	29.7	31.8	.57	1
475 28	3/4x7/8		320	12.5	11.0	12.2	29.7	34.0	.67	1
475 29	13/16x7/8		320	12.5	11.5	12.2	31.8	34.0	.69	1
475 30	7/8x15/16		326	12.8	12.2	12.8	34.0	37.0	.77	1
475 31	15/16x1		337	13.2	12.8	13.9	37.0	41.0	.98	1
475 32	1x1-1/8		346	13.6	13.0	14.2	39.2	43.0	1.1	1
475 33	1-1/16x1-1/4		358	14.0	13.9	15.5	42.0	49.0	1.3	1
475 34	1-1/8x1-5/16		360	14.1	14.6	15.5	45.5	50.0	1.2	1
475 35	1-3/16x1-5/16		360	14.1	14.6	15.5	45.5	50.0	1.3	1
475 36	1-1/4x1-3/8		412	16.2	17.0	18.2	48.2	53.5	1.8	1
475 37	1-5/16x1-1/2		412	16.2	17.0	18.2	48.2	53.5	1.8	1
475 38	1-7/16x1-5/8		440	17.3	18.0	19.5	53.5	60.5	2.3	1
475 39	1-11/16x1-7/8		476	18.7	19.7	21.4	63.0	70.0	2.8	1
475 40	1-13/16x2		500	19.6	21.4	22.4	67.0	73.0	3.4	1


475 90 Set 10 Piece Metric Box Wrenches

Item No.	mm x mm	OAL mm	mm x mm	OAL mm
475 90	475 01 5.5 x 7.0	165	475 06 14.0 x 15.0	238
475 02	6.0 x 7.0	165	475 07 16.0 x 17.0	262
475 03	8.0 x 9.0	180	475 08 18.0 x 19.0	290
475 04	10.0 x 11.0	195	475 09 20.0 x 22.0	320
475 05	12.0 x 13.0	216	475 10 21.0 x 23.0	326

475 91 Set 8 Piece Inch Box Wrenches

Item No.	Inch x Inch	OAL mm	mm x mm	OAL mm
475 91	475 18 1/4 x 5/16	170	475 25 5/8 x 3/4	290
475 20	3/8 x 7/16	195	475 26 11/16 x 3/4	290
475 21	7/16 x 1/2	216	475 29 13/16 x 7/8	320
475 22	1/2 x 9/16	239		
475 23	9/16 x 5/8	239		