


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES, UNLESS OTHERWISE SPECIFIED:

FOR USE WITH PANDUIT™ 3/8", 1/2" AND 5/8" STAINLESS STEEL STRAPPING, .015" AND .020" THICKNESSES.

(IT IS NOT INTENDED FOR USES OTHER THAN PANDUIT™ STAINLESS STEEL STRAPPING.)

GRIPPERS AND NOSE MAY BE REPLACED IN FIELD.

- ◆ REPLACEMENT GRIPPER KIT: KT2MG
- ◆ REPLACEMENT NOSE: BT2N75

TOOL THICKNESS = 1.62" (41.1 mm)

CAD FILENAME/LAYERS

PANDUIT CORP. TINLEY PARK, ILLINOIS
BT2MS75 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
1. (X) \pm 1. (XXX) \pm
1. (XX) \pm ANGLES \pm

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES. THIRD ANGLE PROJECTION.

DRAWN BY B.D. MAT'L:

DATE 7-22-92

CHKD JPW

SCALE **NONE**

DRAWING NO. **TP13608A01**

SIZE **A**

02	01/15/02	WDE	WFM	PHOTO DWG FORMAT™ NO CHANGE	3919	—	LAH		
REV	DATE	BY	CHK	DESCRIPTION	ECN	— R	CUST	SUP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[BT2MS75](#)