


Dimensions (In.)
except where noted



Specifications:

- Primary voltage: 120V 60Hz 12W
- Exciting current, open circuit: 90mA max.
- DC resistance \pm 15%: 125Ω
- Secondary, no load voltage: 13.7VAC
- Loaded voltage: 12VAC @ 500mA
- DC resistance \pm 10%: 1.3Ω
- Rated continuous output power: 6VA
- Insulation resistance: $100M\Omega$ @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute
primary-core: 1,500VAC for 1 minute
secondary-core: 500VAC for 1 minute
- Temperature rise: 65°C max. @ rated load

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[412-212051](#)