



## FIBER OPTIC PATCH CABLE ASSEMBLIES



✓ Active

### TE CONNECTIVITY (TE)

## C/A,F/O,2F I/O MM50 OM3,SCLC DPX

FullAXS | DPU , Fiber Optic

3-2064915-0

TE Internal Number: 3-2064915-0

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

**Cable Type** Fiber Optic

**Fiber Diameter (μm)** 50/125

**Outside Cable Diameter** 7.5 mm [.295 in]

**Number of Fibers** 2

**Connector Color (End A)** Beige

### PRODUCT DRAWING

English

## DOCUMENTATION

Product Drawings

### CABLE ASSEMBLY, FIBER OPTIC, 50/125, OM3, 2 FIBER BREAKOUT CABLE, SEALED CIRCULAR LC DUPLEX (ODVA), BOTH ENDS

PDF

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

## Product Type Features

**Cable Type** Fiber Optic  
**Mode** Multimode  
**Connector Type (End A)** LC  
**Connector Type (End B)** LC  
**Connector Style (End A)** Duplex  
**Connector Style (End B)** Duplex  
**Fiber Type** OM3  
**Fiber Channel** No  
**Product Type** Cable Assembly  
**Cable Assembly Type** LC Duplex to LC Duplex

---

#### Configuration Features

**Number of Fibers** 2  
**Cable Buffering** Tight Buffer  
**Number of Connectors (End B)** 2  
**Number of Connectors (End A)** 2

---

#### Signal Characteristics

**Insertion Loss B (Max) (dB)** .61  
**Insertion Loss A (Max) (dB)** .61

---

#### Body Features

**Connector Color (End A)** Beige  
**Connector Color (End B)** Beige  
**Cable Color** Black  
**Boot Type (Left)** Standard  
**Boot Type (Right)** Standard  
**Boot Color (Left)** Black  
**Boot Color (Right)** Black  
**Polarity** Pair Flipped  
**Ferrule Material** Ceramic

---

#### Dimensions

**Fiber Diameter (µm)** 50/125  
**Outside Cable Diameter** 7.5 mm [.295 in]

---

#### Industry Standards

**Flammability Rating** OFNR (Riser) Jacket

---

#### Other

**Cable Assembly Length (m)** 30

---

### PRODUCT COMPLIANCE



Statement of Compliance

#### Statement of Compliance

PDF

---

