



REV.	MODIFICATION.	DATE	DRN
A	NEW DWG	12/05/94	PTG
B	SCN03-075	29/04/03	OW
03	CO2010308	05/08/08	SF




0.8[0.03] THICK DOUBLE SIDED ADHESIVE TAPE
SEE TABLE FOR DETAILS

TYPICAL RELEASE TAB LOCATION

PART NUMBER	ADHESIVE	"A"	MATERIAL
MWSSEB-1-01A2-RT	ACRYLIC ADHESIVE FOAM TAPE, PE LINER (RMS-24)	9.5[0.37]	NYLON 6/6 UL94-V2(RMS-01)
MWSSEB-1-19A2-RT			NYLON 6/6 UL94-V0(RMS-19)
MWSSEBE-1-01A2-RT		12.7[0.50]	NYLON 6/6 UL94-V2(RMS-01)
MWSSEBE-1-19A2-RT			NYLON 6/6 UL94-V0(RMS-19)

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO
RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR
REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

 Richco®		ALL DIMENSIONS IN mm[Inch] GENERAL TOLERANCES ±0.25 UNLESS OTHERWISE STATED 1 DECIMAL PLACE ±0.25 2 DECIMAL PLACES ± 0.10 ANGULAR ±1°		THIRD ANGLE 	
MATERIAL: SEE TABLE				COLOUR: NATURAL	
DESCRIPTION: MICRO WIRE SADDLE SIDE ENTRY ON BASE				PART No: SEE TABLE	
DRG No: 0606-0002		NPR No: N/A		Mass:(g) 0.8	SHEET SIZE A4
DRN SF	DATE 05/08/08	CHKD TC	DATE 05/08/08	SCALE NTS	SHEET No. 1 OF 1