



Track and Mounting Accessories



Mounting track and holding clips for screw terminal sockets. The Track 24A110 is available in three foot length with mounting holes on 6" centers. Track can be cut to shorter lengths for small chassis assemblies or full sections can be used end-to-end in larger installations. Made of lightweight, sturdy extruded aluminum, track accepts several styles of screw terminal sockets — KU series 27E121, 27E867 and 27E893; Octal Type 27E122, 27E123, 27E891 and 27E892; KH series 27E166 and 27E894; R10 series 27E460, 27E461 and 27E462; and K10 series 27E467 and 27E895. The track will also mount the following relays — KUB, PM, PRD, SSR, SSRD, SSRQ and SSR1.


| Stock No. | Mfr.'s Type | Description                                                                                                                                                                                                            | EACH  |       |       |         |
|-----------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|-------|-------|---------|
|           |             |                                                                                                                                                                                                                        | 1-24  | 25-49 | 50-99 | 100-249 |
| 886-5015  | 24A110      | DIN rail style extruded aluminum mounting track 36" (914 mm) long with holes on 6.0" (152.4 mm) centers; Holes accept #8 screws                                                                                        | 10.39 | 9.34  | 8.48  | 7.83    |
| 886-1504  | 24A071      | Steel mounting clip with one #6-32 screw                                                                                                                                                                               | .63   | .55   | .49   | .46     |
| 886-1502  | 24A072      | Plastic twist mounting clip for 27E166, 27E122 and 27E123 sockets; Twist clip into track to hold socket in place, except when used on end of track; Use 24A071 on ends of track to lock first and last socket in place | .77   | .68   | .61   | .56     |
| 886-1503  | 40G432      | Plastic insulator for track or surface mounting; Use with 27E460, 27E461, 27E462 and 27E867 sockets                                                                                                                    | .76   | .67   | .57   | .53     |

Octal-Style Sockets



For KRP, KRPA, KRP3-H, KAP, KBP, and KCP relays; CD-38, CH, CK, CNS, CNT and CR time delays, and CS sensor. Type 27E122 is molded polycarbonate, 8-pin screw terminal socket, rated 10 amperes. Type 27E123 is molded polycarbonate, 11-pin screw terminal socket, rated 10 amperes. Type 27E891 is 8-pin DIN rail mount, screw terminals. Type 27E892 is 11-pin DIN rail mount, screw terminals.

| Stock No. | Mfr.'s Type | Terminal Type | EACH  |       |       |         |
|-----------|-------------|---------------|-------|-------|-------|---------|
|           |             |               | 1-24  | 25-49 | 50-99 | 100-249 |
| 886-1426  | 27E122      | Screw Term.   | 4.88  | 4.31  | 3.91  | 3.61    |
| 886-1427  | 27E123      | Screw Term.   | 8.05  | 7.24  | 6.58  | 6.08    |
| 886-1606  | 27E891      | Screw Term.   | 6.50  | 5.85  | 5.30  | 4.89    |
| 886-9997  | 27E892      | Screw Term.   | 11.29 | 10.17 | 9.23  | 8.52    |



Sockets for KH Series

For KHS and KHU series relays. 27E006, 4PDT solder terminal socket. 27E007, 4PDT printed circuit socket. 27E166, 4PDT screw terminal socket. 1 oz.

| Stock No. | Mfr.'s Type | Socket Term. | EACH  |       |       |         |
|-----------|-------------|--------------|-------|-------|-------|---------|
|           |             |              | 1-24  | 25-49 | 50-99 | 100-249 |
| 886-1410  | 27E006      | Solder       | 2.08  | 1.75  | 1.56  | 1.28    |
| 886-1411  | 27E007      | P.C.         | 1.97  | 1.70  | 1.55  | 1.42    |
| 886-1404  | 27E166      | Screw        | 11.12 | 10.13 | 9.18  | 8.46    |
| 886-1412  | 20C217      | —            | .47   | .37   | .37   | .32     |
| 886-5001  | 27E894      | Screw        | 15.59 | 14.18 | 12.86 | 11.88   |

\*Hold-down spring.

Mounting Strip for KH Series

Type 37D633 will mount 8KH sockets (except 27E166 and 27E894) in one length of aluminum strip, measuring 10.9 × 2.5 × 0.062".

|                |      |      |
|----------------|------|------|
| 886-1495, 1-24 | EACH | 6.68 |
| 25-49          | EACH | 6.01 |
| 50-99          | EACH | 5.46 |
| 100-249        | EACH | 5.04 |


Relay Accessories

8-Pin "P" Case. Clear plastic, octal base. For mounting rectifiers, capacitors. 4 screws. 2 × 1 13/32 × 1 13/32" (5.08 × 3.57 × 3.57 cm). Weight: 1 oz. (28 gm).


|                        |      |      |
|------------------------|------|------|
| 886-1460, 35D070, 1-24 | EACH | 3.00 |
| 25-49                  | EACH | 2.64 |
| 50-99                  | EACH | 2.40 |
| 100-249                | EACH | 2.21 |

KRP. Hold down spring. Weight: 3 oz. (85 gm).

|                        |      |     |
|------------------------|------|-----|
| 886-1416, 20C176, 1-24 | EACH | .72 |
| 25-49                  | EACH | .63 |
| 50-99                  | EACH | .56 |
| 100-249                | EACH | .52 |



KUP Sockets




SPDT/DPDT/3PDT sockets rated 15 amps snap into a chassis without additional hardware for support. Socket 27E396 has 0.187" quick connect terminals. Hard mount sockets are rated 15 amperes. Will accept 0.187" terminals of all series KU and plain case series KUP relays.

| Stock No. | Mfr.'s Type | Term. Type | EACH  |       |       |         |
|-----------|-------------|------------|-------|-------|-------|---------|
|           |             |            | 1-24  | 25-49 | 50-99 | 100-249 |
| 886-1436  | 27E396      | O.C.       | 4.21  | 3.63  | 3.39  | 2.90    |
| 886-1420* | 27E043      | Solder     | 2.69  | 2.27  | 2.12  | 1.85    |
| 886-1421* | 27E046      | P.C.       | 2.76  | 2.43  | 2.21  | 2.04    |
| 886-1425* | 27E121      | Screw      | 7.35  | 6.62  | 6.00  | 5.54    |
| 886-1422* | 20C228*     | Spring     | .69   | .60   | .55   | .50     |
| 886-5003* | 27E867†     | Screw      | 19.66 | 18.69 | 17.68 | 15.80   |
| 886-5004* | 27E893‡     | Screw      | 10.34 | 9.32  | 8.45  | 7.80    |

\*Type 20C228 hold-down spring. †4 pole. ‡3 pole. \*Hard mount sockets.

Strip Ground Sockets for Series R10 Relays

Types 27E125 and 27E128 are 2PDT sockets, spring ground; Type 27E126 and 27E129, 4PDT socket, spring ground; Type 27E127 is 6PDT socket spring ground. Contact your nearest Allied facility for larger quantity pricing.



| Stock No. | Mfr.'s Type | Terminal Type | EACH  |       |       |         |
|-----------|-------------|---------------|-------|-------|-------|---------|
|           |             |               | 1-24  | 25-49 | 50-99 | 100-249 |
| 886-1430  | 27E125      | Solder        | 1.86  | 1.58  | 1.45  | 1.22    |
| 886-1431  | 27E126      | Solder        | 2.26  | 1.93  | 1.80  | 1.50    |
| 886-1432  | 27E127      | Solder        | 2.82  | 2.42  | 2.25  | 1.90    |
| 886-1433  | 27E128      | PC Term.      | 1.58  | 1.37  | 1.24  | 1.15    |
| 886-1434  | 27E129      | PC Term.      | 1.96  | 1.71  | 1.55  | 1.43    |
| 886-9018* | 27E460      | Screw         | 20.50 | 18.63 | 17.09 | 15.77   |
| 886-9017† | 27E461      | Screw         | 23.53 | 22.34 | 20.38 | 18.93   |

\*2 pole. †4 pole.

Hold Down Springs

| Stock No. | Mfr.'s Type | Poles | EACH |       |       |         |
|-----------|-------------|-------|------|-------|-------|---------|
|           |             |       | 1-24 | 25-49 | 50-99 | 100-249 |
| 886-1440  | 20C249      | 2     | .26  | .22   | .20   | .19     |
| 886-1441  | 20C250      | 4     | .27  | .22   | .20   | .19     |
| 886-1442  | 20C251      | 6     | .30  | .26   | .22   | .19     |



Relay Cover


For Type PRD. Grey enameled heavy steel. Has predrilled mounting holes in base and knockouts for 1/2" (1.27 cm) dia. conduit.

PRD Cover #35D013. Size: 3.125 × 3.375 × 5.312" (13.49 × 8.57 × 7.94 cm). Weight: 1 lb. (454 gm).


|                        |      |       |         |      |       |
|------------------------|------|-------|---------|------|-------|
| 886-1455, 35D013, 1-24 | EACH | 23.49 | 50-99   | EACH | 19.38 |
| 25-49                  | EACH | 21.35 | 100-249 | EACH | 17.88 |

Sockets and Accessories for MT Relays

11 Pin Octal Socket. Multimode 3 pole, standard 32 mm DIN rail mount, suitable for chassis mounting. Measures 2.947 × 1.493 × 1.024 high. Rated: 10 A at 380 V. 8 or 11 Pin Octal Socket. Low cost, 3 pole, standard 32 mm DIN rail mount, suitable for chassis mounting. Measures 2.441 × 1.496 × 1.024. Rated: 10 A at 400 V.



| Stock No. | Mfr.'s Type | Fig. | Description            | EACH |       |         |
|-----------|-------------|------|------------------------|------|-------|---------|
|           |             |      |                        | 1-24 | 25-99 | 100-499 |
| 886-2115  | MT78740     | 1    | 11 Pin Octal Socket    | 5.50 | 5.18  | 4.81    |
| 886-2116  | MT78745     | 2    | 8 Pin Octal Socket     | 5.30 | 4.99  | 4.63    |
| 886-2118  | MR28800     | —    | Plastic Retaining Clip | .97  | .91   | .85     |



Dust Covers for PM and PRD Relays

Heavy steel cover screws in place on sheet metal base. Knockouts accept 0.5" diameter conduit. Pre-drilled mounting holes. Type 35D013 has holes to accept PRD mounting. Type 35D277 accepts PM mounting. Plastic dust cover for PM Series only.

| Stock No. | Mfr.'s Type | Dimensions |        |        | EACH  |       |       |         |
|-----------|-------------|------------|--------|--------|-------|-------|-------|---------|
|           |             | Length     | Width  | Height | 1-24  | 25-49 | 50-99 | 100-249 |
| 886-1455  | 35D013      | 5.312"     | 3.375" | 3.125" | 23.49 | 21.35 | 19.38 | 17.88   |
| 886-1456  | 35D203      | 3.394"     | 2.657" | 2.719" | 5.26  | 4.77  | 4.44  | 3.90    |
| 886-1457  | 35D227      | 5.313"     | 3.812" | 3.812" | 21.42 | 20.37 | 19.29 | 17.77   |