

UniBond

Duct Tape

Issued: 24-May-10

Ref: UT3000

Product Description	Typical Technical Data	Application
Heavy duty, strong, tough and 100% weatherproof*, multi-purpose cloth tape.	Colours: Silver, black, white, orange	Hundreds of uses around the home, garden, garage and workplace.
Carrier: Polyethylene reinforcement with polyester fabric scrim.	Thickness: 220 µm	Fixes, binds, mounts, repairs, bundles, joins, seals, reinforces, protects and identifies.
Adhesive: Extra high strength synthetic rubber.	Width: 50mm	Suitable for interior and exterior use.
	Tensile Strength (N/cm): 45	Easy to tear by hand.
	Elongation at break (%): 25	Limitations: Not intended for permanent repairs.
	Peel adhesion (N/cm): 17	Not suitable for use on glass.
	Unwind force (N/cm): 3	*Not suitable for total immersion in water, e.g. pond liners, children's pools.
	Temperature range °C: -5 to + 60	

The above data and performance characteristics are compiled on the results of tests and estimates based on careful calculations. They are put forward in good faith but are not guaranteed. In particular the customer should satisfy himself of the suitability of the product for its intended use and consult us if he is in any doubt about any particular application.

The conditions under which this product is stored affect its performance. Storage should be in dry well ventilated rooms with a reasonably consistent temperature around 20°C and protected from continuous exposure to direct sunlight. The product should always be applied to clean dry surfaces.