







ASSEMBLY - VIEW FROM FRONT




ASSEMBLY - VIEW FROM BOTTOM



SECTION A-A



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM SIDE

1583T6A1BKX
Finish - Front - Black Painted Steel
Back - Black Painted Steel
Rated - 125 VAC, 60 Hz, 15 Amps
Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)
- UL Recognized Standard UL1363
Cord Length
1583T6A1BKX - 6' Foot Power Cord (NEMA 5-15P)
1583T6B1BKX - 15' Foot Power Cord (NEMA 5-15P)

