

NOTES:

1. Rating:300V 20A(UL);
2. Insulation Withstanding Voltage:AC2000V/MIN
3. Insulation Resistance: $\geq 500M\Omega$ or more at DC500V
4. Temperature Range: $-33^{\circ}C/+105^{\circ}C$
5. Screw Torque Vlaue:4.5 lbf-in(UL)
6. Suitable Electric Wire: 12-20AWG
8. Housing: Nylon PA66
9. Screw M3, Stell, Zinc Plated
10. Standard Color: Natural

20.47

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF ON-SHORE
TECHNOLOGY, INC. AND SHALL NOT BE
REPRODUCED, COPIED OR USED IN ANY
MANNER WITHOUT THE PRIOR WRITTEN
CONSENT OF ON-SHORE TECHNOLOGY,
INC.