

PermaSleeve® Wire Marking Sleeves

www.BradyID.com

3" Core Wire & Cable Materials:

B-7641 PermaSleeve® Single-Sided Low Halogen Polyolefin Wire Marking Sleeves:

Use the table below to browse all available single-sided printing, 1.5" width B-7641 PermaSleeve® ZH Low Halogen Polyolefin Wire Marking Sleeves or build your own catalog number on page 172.

Single-Sided Printable, 1.5" Sleeve Width

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm) Min. Max.	Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
ZH-094-150-WT	White	2,500	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	.021 (0.5) ± .004 (0.1)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-094-150-WT-**	White	2,500	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	.021 (0.5) ± .004 (0.1)	--	PR Plus	R4300/ R6602
ZH-094-150-WT-S	White	500	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	.021 (0.5) ± .004 (0.1)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-125-150-WT	White	2,500	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	.025 (0.6) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-125-150-WT-**	White	2,500	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	.025 (0.6) ± .003 (0.07)	--	PR Plus	R4300/ R6602
ZH-125-150-WT-S	White	500	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	.025 (0.6) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-187-150-WT	White	2,500	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	.025 (0.6) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-187-150-WT-**	White	2,500	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	.025 (0.6) ± .003 (0.07)	--	PR Plus	R4300/ R6602
ZH-187-150-WT-S	White	500	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	.025 (0.6) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-250-150-WT	White	1,000	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	.029 (0.7) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-250-150-WT-**	White	1,000	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	.029 (0.7) ± .003 (0.07)	--	PR Plus	R4300/ R6602
ZH-250-150-WT-S	White	250	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	.029 (0.7) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-375-150-WT	White	1,000	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	.028 (0.7) ± .002 (0.05)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-375-150-WT-**	White	1,000	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	.028 (0.7) ± .002 (0.05)	--	PR Plus	R4300/ R6602
ZH-375-150-WT-S	White	250	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	.028 (0.7) ± .002 (0.05)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-500-150-WT	White	500	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	.028 (0.7) ± .002 (0.05)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-500-150-WT-**	White	500	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	.028 (0.7) ± .002 (0.05)	--	PR Plus	R4300/ R6602
ZH-500-150-WT-S	White	250	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	.028 (0.7) ± .002 (0.05)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-750-150-WT	White	250	2 to 4/0	0.375 (9.5) - 0.700 (17.8)	0.750 (19.0)	0.375 (9.5)	.031 (0.8) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-750-150-WT-**	White	250	2 to 4/0	0.375 (9.5) - 0.700 (17.8)	0.750 (19.0)	0.375 (9.5)	.031 (0.8) ± .003 (0.07)	--	PR Plus	R4300/ R6602
ZH-750-150-WT-S	White	100	2 to 4/0	0.375 (9.5) - 0.700 (17.8)	0.750 (19.0)	0.375 (9.5)	.031 (0.8) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-1000-150-WT	White	250	2/0 to 0.950" dia.	0.450 (11.4) - 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	.036 (0.9) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-1000-150-WT-**	White	250	2/0 to 0.950" dia.	0.450 (11.4) - 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	.036 (0.9) ± .003 (0.07)	--	PR Plus	R4300/ R6602
ZH-1000-150-WT-S	White	100	2/0 to 0.950" dia.	0.450 (11.4) - 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	.036 (0.9) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-1500-150-WT	White	250	N/A	0.750 (19.0) - 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	.038 (1.0) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-1500-150-WT-S	White	100	N/A	0.750 (19.0) - 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	.038 (1.0) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-2000-150-WT	White	100	N/A	1.000 (25.4) - 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	.038 (1.0) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
ZH-2000-150-WT-S	White	50	N/A	1.000 (25.4) - 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	.038 (1.0) ± .003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602

*Choosing Your PermaSleeve Color

While white and yellow are standard colors, you may special order your sleeves in the colors listed below. Replace WT or YL with the abbreviation of the desired color.

Example: ZH-094-2-WT-S becomes ZH-094-2-RD-S

Standard Stock Colors:

WT = White
YL = Yellow

Special Order Colors:

(Contact Brady Customer Service for availability)

BK = Black GY = Gray RD = Red
BL = Blue OR = Orange VT = Violet
GR = Green PK = Pink

** Choosing Your PermaSleeve Pieces (optional):

While 1 or 2 markers per sleeve is standard, you may also choose to have each sleeve slit multiple times to produce multiple pieces. Simply replace the double asterisks (**) in the catalog number to fill in your desired pieces per marker.

Example: ZH-187-2-WT-S-** becomes ZH-187-2-WT-S-4


This "4" means that this 2.000" sleeve is slit into four 0.500" pieces.

Standard Options:

1 or 2 markers per sleeve

Other Available Slit Options:

3 or 4 markers per sleeve
(Contact Brady Customer Service for availability)



Note: White and yellow are standard stock. All other colors available as special order.

Approx. wire gauge based on AWG for THHN wire.

View the Material Brands & Attributes Guide on page 4.

Benchtop Printer Ribbons on page 184.

Full Material Properties on page 187.

1-888-272-3946 | www.BradyID.com