




< List of part numbers with package codes >  
DEHC32H471KA2B

### Shape



L size or outer diameter D (mm)	6.0 mm max.
T size	4.0 mm max.
Lead spacing F	$5.0 \pm 1.0$ mm
Lead diameter d	$0.6 \pm 0.05$ mm
Paint dripping e	Up to the end of crimp

### Notes

Please use replacement

### References

Packaging	Specifications	Minimum quantity
B	Packing in bulk	500

### Specifications

Capacitance	470pF ± 10%
Rated voltage	500Vdc
Temperature characteristics (complied standard)	C(JIS)
Capacitance change rate (1)	± 20%(-25 to 85 °C)
Capacitance change rate (2)	+15/-30%(85 to 125 °C)
Temperature range of temperature characteristics	-25 to 125
Operating temperature range	-25 to 125

1 of 1

### Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.