



	10	9	8	7	6	5	4	3	2	19070					
	LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS										
	MATERIAL NUMBER	ALTERNATE NUMBER	MATERIAL NUMBER	ALTERNATE NUMBER	HOUSING COLOR	STUD SIZE	"S" $\pm .005/(0.13)$	"W" MAX.	"C" MIN.	"L" MAX.	"ID" MIN.	STOCK THICKNESS REFERENCE	"H" $\pm .020/ .051$		
F	I90700005	AA-220-02X	I90700006	AA-220-02XT	RED	2	.094/(2.39)	.235/(6.00)	.157/(3.99)	.709/(18.01)	.062/(1.57)	.028/(0.71)	.980/(24.89)	F	
	I90700007	AA-220-04X	I90700008	AA-220-04XT	RED	4	.119/(3.02)								
	I90700009	AA-220-06X	I90700010	AA-220-06XT	RED	6	.146/(3.71)								
	I90700011	AA-221-06X	I90700012	AA-221-06XT	RED	6	.146/(3.71)								
E	I90700013	AA-221-08X	I90700014	AA-221-08XT	RED	8	.173/(4.39)	.322/(8.18)	.270/(6.86)	.866/(22.00)	.062/(1.57)	.028/(0.71)		.980/(24.89)	E
	I90700015	AA-221-10X	I90700017	AA-221-10XT	RED	10	.198/(5.03)								
	I90700019	AA-221-209X	I90700020	AA-221-209XT	RED	M5	.209/(5.18)								
	I90700021	AA-222-10X	I90700022	AA-222-10T	RED	10	.198/(5.03)	.477/(12.11)	.386/(9.80)	1.060/(26.92)	.062/(1.57)	.028/(0.71)			
I90700023	AA-222-14X	I90700024	AA-222-14XT	RED	14	.265/(6.73)									
	-	-	I90700601 (C2)	AA-222-14XT-BK	BLACK	14	.265/(6.73)								
D	I90700026	AA-222-56X	I90700027	AA-222-56XT	RED	5/16"	.328/(8.33)	.544/(13.82)	.552/(14.02)	1.259/(31.98)	.055/(1.40)	.031/(0.79)	1.172/(29.77)	D	
	I90700029	AA-226-10X	I90700030	AA-226-10XT	RED	10	.198/(5.03)								
	I90700031	AA-226-14X	I90700032	AA-226-14XT	RED	14	.265/(6.73)								
	I90700036	AA-226-56X	I90700037	AA-226-56XT	RED	5/16"	.328/(8.33)								
	I90700033	AA-226-38X	I90700035	AA-226-38XT	RED	3/8"	.390/(9.91)	.264/(6.70)	.240/(6.10)	.807/(20.50)	.062/(1.57)	.028/(0.71)			.980/(24.89)
	I90700038	AA-232-04X	I90700039	AA-232-04XT	RED	4	.119/(3.02)								
	I90700040	AA-232-06X	I90700042	AA-232-06XT	RED	6	.146/(3.71)								
	I90700044	AA-232-08X	I90700045	AA-232-08XT	RED	8	.173/(4.39)								
	I90700051	AA-233-10X	I90700052	AA-233-10XT	RED	10	.198/(5.03)	.283/(7.20)	.240/(6.10)	.816/(20.73)	.062/(1.57)	.028/(0.71)			

(C2)



SALES DRAWING

- NOTE(S):
1. MATERIAL: COPPER
PLATING: ELECTROPLATE TIN
 2. DELETED
 3. INSULATION: MOLDED PVC, SEE CHART FOR COLOR (C2)
 4. MWID=MAXIMUM WIRE INSULATION DIA.
 5. ALL DIMENSIONS IN INCHES (MM).
 6. PARTS ARE ROHS COMPLIANT.

REDRAW, ADD BLACK HSG EC NO: WNA2011-0382 IDRW: NETHRODAHL 2011/01/20 CHKD: APPR: JMACNEIL 2011/02/21 DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY DMYRICK	DATE 2005/7/22	TITLE RING TONGUE TERMINAL INSULKRIMP, 200-SERIES 22-18 AWG			
		4 PLACES	± ---	± ---	CHECKED BY	DATE				
		3 PLACES	± ---	± ---	HBEITZEL	2005/7/22				
		2 PLACES	± ---	± ---	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED			
		1 PLACE	± ---	± ---	RDEROSS	2005/7/22				
		ANGULAR ± ---°		MATERIAL NO.	DOCUMENT NO.	SHEET NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-19070-003		1 OF 1		
		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						