



General ordering data

Order No.	0106020000
Part designation	SAKT 2/35/LT 4STB
Version	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
EAN	4008190182892
Qty.	50 pc(s).

Product notes

Note, technical data	10 mm ² stranded and AWG 8/7 connections are to be fixed with 1.6 Nm tightening torque.
Function	4 sockets 14 KrG 60 V*
Note, accessories	To safe the test sockets use the SDIZ-blade (see chapter Tools) or bits with pilots!

Additional technical data

Colour of insulating material	Medium yellow
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 130 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Test-disconnect terminals

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	6 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.5 mm ²
Clamping range, max.	10 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	12 mm
Clamping screw	M 3.5
Blade size	4.0 x 0.8 mm
Tightening torque range	1.2...1.6 Nm
Torque level with DMS electric screwdriver	3
Gauge to IEC 60947-1	A5
Solid, min.	0.5 mm ²
Solid, max.	10 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	10 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	6 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	6 mm ²

Dimensions

Width	8 mm
Height of lowest version	52.5 mm
Length	82 mm
TS 32 offset	24 mm
TS 35 offset	41 mm

Disconnect terminals

Cross-disconnect	without
Integral test socket	Yes
Slitting	sliding
Tightening torque range	0.5...0.8 Nm
Torque level with DMS electric screwdriver	3

Rating data

Rated cross-section	6 mm ²
Rated voltage	125 V
Rated impulse voltage	6 kV
Rated current	41 A
Standards	IEC 60947-7-1
Current with max. conductor	46 A
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	25 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 8

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000902
ETIM 3.0	EC000902
eClass 4.1	27-14-11-26
eClass 5.0	27-14-11-26
eClass 5.1	27-14-11-26

Similar products

Order No.	Part designation	Version
0105820000	SAKT 1/35/DU1	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105420000	SAKT 1/35/LT	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105620000	SAKT 1/35/LT STB	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105720000	SAKT 1/35/QT1	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0124620000	SAKT 1/35/QT2	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105920000	SAKT 2/35/LT/STB	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
1272420000	SAKT 4/35/LT O.STB	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, KrG, Medium yellow, TS 35
1272520000	SAKT 4/35/LT STB2.0	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, KrG, Medium yellow, TS 35
1289920000	SAKT 4/35/LT STB2.3	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, KrG, Medium yellow, TS 35