

[illegible]

- Operating Frequency: 120 operations
- Life: 1,000,000 operations min.
- Operating Temperature: 0°C ~ 65°C
- Storage Temperature: -25°C ~ 85°C

- RoHS Compliant and process compatible with 260° solder

- Rating: 3A/125VAC; 0.2A/60VDC
- Operating Frequency: 10~30 operations
- Contact Resistance (initial): 30~100mΩ max.
- Insulation Resistance (at 500VDC): 100MΩ min.
- Dielectric Strength: 1,000VAC RMS (50-60Hz)
- Life (at rated load): 6,000~15,000 operations

- OF Max. (g): 150
- OP (mm): 7.0 ± 0.3
- PT Max. (mm): 1.3
- OT Min. (mm): 0.2
- MD Max. (mm): 0.3
- FP Max. (mm): 8.0
- RF Min. (g): 20

Mountain Switch

1-800-346-6873