

SPECIFICATIONS





PARAMETERS	VALUES	UNIT
RATED VOLTAGE (SQUARE WAVE)	5	Vp-p
OPERATING VOLTAGE RANGE	3 ~ 7	Vp-p
RATED CURRENT (MAX)	70	mA
COIL RESISTANCE	32 ± 5	OHM
MINIMUM SPL @ 10 CM	87	DBA
RESONANT FREQUENCY	$2,300 \pm 500$	Hz
OPERATING TEMPERATURE	$-30 \sim +70$	°C
STORAGE TEMPERATURE	$-40 \sim +80$	°C
HOUSING MATERIAL	LCP	-
TERMINAL MATERIAL	Sn PLATED PHOSPHOR BRONZE	-
WEIGHT	.42	grams

THIS DOCUMENT CONTAINS DATA PROPRIETARY
TO PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED,
INC. IS PROHIBITED.
©2003, Projects Unlimited Inc.

REVISION HISTORY

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	4/1/2005	
A	UPDATED RoHS INFORMATION	5/9/2005	R.W.
B	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	11/1/2007	B.R.

A (5 : 1)



DETAIL "B"



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE 43°.	SIZE	Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date	
		G.V.	3/31/2005	E.P.	4/1/2005	R.W.	4/1/2005	11/1/2007	
SMT-0823-S-R									
Transducer (Electro-Mech)		Edition	-	Sheet	1 / 1				

 pui audio™ inc
a projects unlimited company

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMT-0823-S-R](#) [SMT-735](#) [SMT-1324-TW-12V-R-T/R](#)