




## Lötstifte Picots pour C.I. Soldering lugs for PCB

|                                               |                                                                                   |                                                                                   |                                                                                   |                                                                                   |                                                                                     |                                                                                     |
|-----------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                                               |  |  |  |  |  |  |
| Artikelnummer<br>Numéro d'article<br>Part-No. | <b>1002p.6</b>                                                                    | <b>01002p.6</b>                                                                   | <b>1002b.6</b>                                                                    | <b>01002b.6</b>                                                                   | <b>1004q.6</b>                                                                      | <b>01004q.6</b>                                                                     |
| Bohrung/Trou/Hole                             | Ø 1.1<br>T 4<br>L 10.3<br>B1 3<br>N 1.8<br>N1 2.8<br>øD<br>B 1.1<br>S 0.6         | Ø 1.1<br>T 4<br>L 10.3<br>B1 3<br>N 1.8<br>N1 2.8<br>øD<br>B 1.1<br>S 0.6         | Ø 1.1<br>T 6.6<br>L 13<br>B1 2.2<br>N 1<br>N1 2.7<br>øD<br>B 1.1<br>S 0.5         | Ø 1.1<br>T 6.6<br>L 13<br>B1 2.2<br>N 1<br>N1 2.7<br>øD<br>B 1.1<br>S 0.5         | Ø 1.2<br>T 1.5<br>L 8<br>B1 1.9<br>N 0.7<br>N1 1.2<br>øD 0.8<br>B 1.2<br>S 0.8      | Ø 1.2<br>T 1.5<br>L 8<br>B1 1.9<br>N 0.7<br>N1 1.2<br>øD 0.8<br>B 1.2<br>S 0.8      |
| Werkzeuge<br>Outils<br>Toolings               | <b>14</b>                                                                         | <b>1040r</b>                                                                      | <b>7</b>                                                                          | <b>1040b</b>                                                                      | <b>75</b>                                                                           | <b>1050108</b>                                                                      |

|                                               |                                                                                    |                                                                                    |                                                                                    |                                                                                    |                                                                                      |                                                                                      |                                                                                      |
|-----------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                                               |  |  |  |  |  |  |  |
| Artikelnummer<br>Numéro d'article<br>Part-No. | <b>1003f.6</b>                                                                     | <b>1004b.2</b>                                                                     | <b>01004b.2</b>                                                                    | <b>1003a.2</b>                                                                     | <b>1003b.2</b>                                                                       | <b>1003c.6</b>                                                                       | <b>01003c.6</b>                                                                      |
| Bohrung/Trou/Hole                             | Ø 1.2<br>T 2.2<br>L 14.8<br>B1 2.5<br>N 1.2<br>N1 2.5<br>øD<br>B 1.2<br>S 0.5      | Ø 1.2<br>T 2.4<br>L 11.4<br>B1 2<br>N 0.8<br>N1 1<br>øD 0.8x1.5<br>B 1.25<br>S 0.5 | Ø 1.2<br>T 2.4<br>L 11.4<br>B1 2<br>N 0.8<br>N1 1<br>øD 0.8x1.5<br>B 1.25<br>S 0.5 | Ø 1.2<br>T 2.5<br>L 7<br>B1 2<br>N 0.9<br>N1 1<br>øD<br>B 1.2<br>S 0.5             | Ø 1.2<br>T 2.5<br>L 7.5<br>B1 2.5<br>N 0.8<br>N1 1.6<br>øD<br>B 1.2<br>S 0.15        | Ø 1.2<br>T 2.5<br>L 8.5<br>B1 3<br>N 0.8<br>N1 2.2<br>øD 1.2<br>B 1.2<br>S 0.5       | Ø 1.2<br>T 2.5<br>L 8.5<br>B1 3<br>N 0.8<br>N1 2.2<br>øD 1.2<br>B 1.2<br>S 0.5       |
| Werkzeuge<br>Outils<br>Toolings               | <b>11</b>                                                                          | <b>11</b>                                                                          | <b>1044b</b>                                                                       | <b>4</b>                                                                           |                                                                                      | <b>53</b>                                                                            | <b>1049c</b>                                                                         |

|                                               |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |
|-----------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                                               |  |  |  |  |  |  |
| Artikelnummer<br>Numéro d'article<br>Part-No. | <b>1015k.6</b>                                                                      | <b>01015k.6</b>                                                                     | <b>1003m.2</b>                                                                      | <b>01003m.2</b>                                                                     | <b>1003l.6</b>                                                                        | <b>01003l.6</b>                                                                       |
| Bohrung/Trou/Hole                             | Ø 1.2<br>T 2.6<br>L 5.6<br>B1 2<br>N 0.8<br>N1 1.7<br>øD<br>B 1.2<br>S 0.4          | Ø 1.2<br>T 2.6<br>L 5.6<br>B1 2<br>N 0.8<br>N1 1.7<br>øD<br>B 1.2<br>S 0.4          | Ø 1.2<br>T 3<br>L 8.5<br>B1 2.5<br>N 1.3<br>N1 1.4<br>øD 1.4<br>B 1.25<br>S 0.6     | Ø 1.2<br>T 3<br>L 8.5<br>B1 2.5<br>N 1.3<br>N1 1.4<br>øD 1.4<br>B 1.25<br>S 0.6     | Ø 1.2<br>T 3.5<br>L 11.5<br>B1 2.2<br>N 1.2<br>N1 2.2<br>øD 1.2x2.2<br>B 1.3<br>S 0.5 | Ø 1.2<br>T 3.5<br>L 11.5<br>B1 2.2<br>N 1.2<br>N1 2.2<br>øD 1.2x2.2<br>B 1.3<br>S 0.5 |
| Werkzeuge<br>Outils<br>Toolings               | <b>4</b>                                                                            | <b>1050d</b>                                                                        | <b>9</b>                                                                            | <b>105006</b>                                                                       | <b>11</b>                                                                             | <b>1049l</b>                                                                          |