




Dimensions (In.)

Specifications:

- Rating: 100VAC 1A max or 12VDC 2A max
- Insulation resistance: 50M Ω min @ 250VDC
- Dielectric strength: 250VAC for 1 minute
- Contact resistance: 30m Ω max
- Insertion force: 4.5Kg max
- Withdrawal force: 0.9Kg ~ 3Kg

Part	Material
1 Body	PBT+15%GF UL94V-0
2 Cover	PBT+15%GF UL94V-0
3 Earth Terminal	BS-H0.4t Nickel Plate
4 Connector	BS-H0.5t PbSn Plate

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-2209](#)