



MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE3-3AK




NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - NEMA 1, 3, 4, 12 AND 13 SEALING
- 3 - SIDE EXIT CABLE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 2.7 LB MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE — — — — 1.0 LB MIN		ONE PLACE	(.01)	±.030
DIFFERENTIAL TRAVEL — — — .004 MAX	5A — 250 VAC 1/10HP — 125 OR 250 VAC	TWO PLACE	(.00)	±.015
OVERTRAVEL — — — — — .118 MIN		THREE PLACE	(.000)	±.005
		ANGLES		±
		WEIGHT		

914CE3-3AK

M

DRAWING
NUMBER

1

ISSUE

RELEASE NO. CO-69061 REPLACES

CHECK

REVISIONS

CHECK

DDM/CAD

DRAWN

SA V 10 OCT 91 CHECK