



SPECIFICATION:

- Transmission Bandwidth : DC (50Hz) to 8MHz
- Transmission Distance : 600 Metres (24 AWG UTP) Max.
- Insertion Loss : < 2 dB
- Signal Return Loss : $\geq -15\text{dB}$
- Common Mode Rejection : $\geq -40\text{dB}$ @ 8MHz
- Signal Voltage : 0.5 to 1.5V rms



NOTE:

Video only, Yellow RCA Female to Toolles IDC,
for Keystone mounting

5	PCB SET (TRANSFORMER 1:1)	1 Set	
4	TOOLLESS IDC	1 Set	
3	PLASTIC HOUSING	1 Set	
2	RCA Keystone Housing	1 Set	
1	RCA FEMALE SOLDER TYPE (COLOR: Yellow insert in RCA Female)	1 Set	
NO.	DESCRIPTION	Q'TY	NOTE

DIMENSIONS ARE IN mm (inches)	TOLERANCES ARE FRACTIONS DECIMALS ANGLES	MATERIAL	VIDEO RCA BALUN, KEYSTONE MOUNT, YELLOW				P/N 50-7715	DRAWN	DATE 12/16/2005
MOLD NO.	.X ± 0.25 .XX ± 0.10	FINISH					PROJECT NO.		
50-7715		COLOR					SCALE 1:1	SIZE A4	SHEET 1 OF 1