

C28 K Type



Food Thermometer - type K thermocouple

The new C28 K Type Thermometer - Now with BioCote® Protection

- * Stylish new case, waterproof to IP67 standards
- * NSF Certified
- * Countdown timer
- * Exceptional battery life of up to 7000 hours
- * Permanent clock display
- * Sub-miniature connector for use with wide range of Comark type K probes
- * °F or °C scales
- * Data hold function
- * Easy to use keypad and large LCD display
- * Auto switch-off
- * Built-in protective boot
- * Interactive cell-phone style menu for selection of

Scales

Clock adjustment

Countdown timer - can be stopped during countdown, uses include monitoring how long probe is inserted to obtain accurate reading or monitoring cooking and cooling times. Timer beeps to advise end of timed period

Selectable auto switch-off, with choice of time period before the instrument turns off - 3 minutes, 10 minutes or 30 minutes

- * Two-year warranty

C208 K Type Thermometers with BioCote® Protection

BioCote® is a silver based anti-microbial agent that is impregnated into the instrument case during moulding. BioCote® effectively inhibits the function, growth and reproduction of a wide range of micro-organisms and its protection is increasingly accepted as part of HACCP, due diligence and health and safety procedures. BioCote® protection lasts for the life of the instrument, because the agent is present throughout the case plastic and cannot rub off or be washed or leached out.

BioCote® active ingredients are registered with the US Environmental Protection Agency (EPA).

Although BioCote® inhibits the growth of micro-organisms on the instrument case, it does not protect individuals against such harmful organisms or remove the need to maintain the highest standards of personal and product hygiene and

cleanliness.

Sensor Type	K type thermocouple
Measurement Range	-200 to +600°C, -328°F to +1112°F
Scales	°F and °C
Displayed Resolution	
Above -100°	0.1°
Equal to or less than -100°	1°
Instrument Accuracy at +73°F/+23°C	0.1% ±0.2°C/0.4°F
Operating Temperature Range	-4°F to +122°F/-20°C to +50°C
Display	4 digit, 12.5 mm LCD
Countdown Timer Interval	1 second to 24 hours
Battery	2 x Type I.E.C. LR6 Size AA
Battery Life (continuous)	Up to 7000 hours
Environmental Protection	IP67 BS EN 60529 IEC 529
Dimensions	
Length	152mm/6 inches
Width	58mm/2.3 inches
Depth	22/27mm/0.9/1.1 inches
Weight	128g/4.5 oz