


Model 4163 Insulated Triple Banana Jack Polarized



FEATURES:

- Mounts in panels at .1778 (.70) thickness
- Accepts standard banana plugs up to .80 long.
- Initial connection made with ground receptacle.

MATERIALS:

Banana Jack: Bright Tin Plated Brass
 Marking: "Pomona 4163"
 Mounting Screws: Steel
 Insulation: Polycarbonate
 Lockwasher and Hex Nuts: Steel

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.
 Hands free testing in controlled voltage environments: 2500 WVDC Max.
 Operating Temperature: +115°C (+239°F) Max.
 Current: 15 Amperes

ORDERING INFORMATION: Mode 4163-*

*=Color, -0 Black

Ordering Example: 4163-0 Color is Black.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA