


Date	Rev.	Description



NOTE:

1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	22	20	18	16
AMP.	3	4	7	10
2. MAXIMUM ELECTRICAL RATING : 75°C 300 VOLTS MAX.
3. INSULATION MATERIAL : VINYL
4. INSULATION COLOR : RED
5. TERMINAL MATERIAL : BRASS
6. WIRE RANGE : 22-16 A.W.G.($0.5\text{--}1.5 \text{ mm}^2$)
7. TERMINALS SURFACE TREATMENT : TIN PLATED
8. NEBA TAB : $0.032 * 0.250$ ($0.8 * 6.35$)
9. THICKNESS : 0.40 mm

Tolerance Unless Otherwise Specified	
0 > 6 mm ± 0.20	ANGLE
6 > 18 mm ± 0.30	0° REF $\pm$
18 > 30 mm ± 0.40	0° $\pm$
30 > 75 mm ± 0.50	0° $\pm$

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.	
		JAMECO NO. 109112	GOLDSUN NO. FDFV1-250
DRAWN: Kiki Chen		Description COVER DISCON	Rev. 1
VERIFY PEOPLE: Ada Zheng , Ivy Lan		UNIT: mm	CAS No: ERN No:
		SCALE:	SHEET 1 OF 1