

M8 Actuator/Sensor Distribution Boxes

ASBSM.../LED




4-, 6-, 8-, and 10-Ports (LED)

Pluggable miniature actuator/sensor distribution box with LED operation and function indicators, top-entry, 4-10-ports, M8 socket, 3-poles, 1 signal per socket, M12 connection for the control cable.

— control cable type: RKT12-348/...M or RKWT 12-348/...M —


4-Ports




Pin Assignments

M8 / M12


Wiring Diagrams




4-Ports




6-Ports



8-Ports



10-Ports



ASBSM 4/LED 3 | ASBSM 6/LED 3 | ASBSM 8/LED 3 | ASBSM 10/LED 3

Technical drawing of the 18x1 connector showing side and top views with dimensions.

Side View Dimensions:

- Overall width: 25.5
- Distance from mounting edge to first pin center: 16.8
- Pin pitch: 12
- Mounting hole diameter: $\varnothing 4.1$
- Distance from mounting edge to last pin center: 28.8

Top View Dimensions:

- Overall width: 30
- Distance from mounting edge to first pin center: 16
- Pin pitch: 23
- Distance from mounting edge to last pin center: 18.4
- Mounting hole diameter: $\varnothing 4.1$
- Distance from mounting edge to last pin center: 28.8

[illegible]

$\leq 5\text{m}\Omega$
 10-30 V DC
 1.5 A per port
 1.5 A max. total