

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



TE Part Number: 1 - 1374611 - 0

 Active

 Add to Part List

Not EU RoHS or ELV Compliant ([Find RoHS Compliant Alternates](#))

- ? Cable Assembly
- ? Fiber Type = SM
- ? Cable Assembly Type = SC to LC
- ? LC Connector, SC Connector
- ? Singlemode

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

- [CABLE ASSY, FIBER OPTIC, 1.6mm SINGLEMODE LDS, AMP S...](#)
(PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

List all Documents

Additional Information:

- ## ? Product Line Information

Related Products:

- ## ? Tooling

Product Features

Product Type Features:

- ? Product Type = Cable Assembly
 ? Cable Assembly Type = SC to LC
 ? Connector = LC, SC

Termination Related Features:

- ? Mode = Singlemode
- ? Insertion Loss (dB) = 0.20

Body Related Features:

- ? Fiber Type = SM
- ? Cable Diameter (mm [in]) = 1.60 [.063]
- ? Number of Fibers = 1
- ? Flammability Rating = Low Smoke (PVDF)
- ? Cable Color = White
- ? Length (M [ft]) = 10.00 [32.808]
- ? Ferrule Material = Ceramic

Contact Related Features:

- ? Boot Body Style - Left = Standard
 ? Boot Color - Left = White
 ? Boot Body Style - Right = Standard
 ? Boot Color - Right = White
 ? Fibre Channel = No

Configuration Related Features:

- ? Cable Type = Buffered Fiber
- ? Cable Buffering = Tight
- ? Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°

Industry Standards:

- ? RoHS/ELV Compliance = Not ELV/RoHS compliant
- ? Lead Free Solder Processes = Not relevant for lead free process

Other:

- ? Brand = AMP