


2 19
2018 7-101

Additional accessories for drills

458-569

File of
Accessories
S. 12. 1989
Post number


Drill bit depot



Content:
HSS drill bits, 3-4-5-6-8 mm dia.
Masonry drill bits, 5-6-8 mm dia.

11 9 2 607 018 117

Depth stops



Plastic L=210 mm with scale	for auxiliary handle 1 612 025 024	20	1	1 613 001 005
Plastic L=210 mm without scale	for auxiliary handle 2 602 025 024	20	1	2 607 010 026
Plastic L=210 mm without scale	for auxiliary handle 2 602 025 032	20	1	1 613 001 010
Plastic L=310 mm without scale	for auxiliary handle 2 602 025 032	20	1	1 613 001 003

Drill bit sharpener S 41



For drill bits with 2.5-10 mm diameter. Fits onto drills with 43 mm spindle collar, optimum speed 2000-3000 rpm, angle 118°

3 1 2 607 990 050

Replacement grinding disc

7 1 2 608 600 029

Belt clip



20 1 2 608 040 050

Carrying strap



For all machines with spindle collar diameter 43 mm

20 1 1 605 439 002

Auxiliary handles



For all machines with spindle collar diameter 43 mm

with drill bit depot	20	1	1 612 025 024
without drill bit depot	20	1	2 602 025 032
	20	1	2 602 025 077

Angle piece



For adjusting auxiliary handle, with one each inside and outside thread M14, for Bosch 1430 impact wrench

20 1 1 603 527 017

Drilling angle controller



For right angled holes when free hand drilling. Can be used horizontally and vertically. Angles can also be read from 90° up to +/- 15°. Can be used with all Bosch drills, fits over auxiliary handle.

21 1 1 608 190 006

Can also be used with other makes of drills - recommended for use with the auxiliary handle.

21 1 1 612 025 024

DRILL STANDS AND MACHINE VICES

Description	Dimensions	Part Number	Ex VAT	Ex VAT
Machine Vices: Heavy Duty DIY				
For all Bosch DIY drill stands. Strong die cast aluminium body. Quick clamping mechanism and heavy duty spindle for high clamping pressure. Black chrome plated jaws with deep vertical and horizontal grooves and recesses for flat work pieces.				
Quick clamping machine vice MS65				
Jaw opening	65mm	2 608 030 053	21.91	25.74 AT
Slot spacing	30mm			
Quick clamping machine vice MS80				
Jaw opening	80mm	2 608 030 055	30.68	36.05 AT
Slot spacing	35mm			
Machine Vices: Heavy Duty Trade/Industrial				
For all Bosch DIY and industrial drill stands. Sturdy cast iron body with long profiled handle and heavy duty spindle for maximum clamping pressure. Black chrome plated jaws with deep vertical and horizontal grooves and recesses for flat work pieces. Guided jaws for secure clamping even at the sides of the vice.				
Machine Vice MS 80G				
Jaw opening	80mm	2 608 030 056	47.86	58.24 AT
Slot spacing	100mm			
Machine Vice MS 100G				
Jaw opening	100mm	2 608 030 057	70.04	82.30 AT
Slot spacing	135mm			
Drill Stands				
DIY Drill Stand BS2				
80mm plunge in one, 70° movement of the arm. All adjustments made with quick release levers. Cable holder for added safety. The head can be rotated 360° on the column.				
Overall height	450mm	2 608 180 001	43.79	51.45 AT
Free overhang	125mm			
Base plate	160 x 165mm			
Clamping diameter	43mm			
Weight	2.3kg			
Heavy Duty DIY Drill Stand BS7				
80mm plunge in one, 180° movement of the arm. All adjustments made with quick release levers. Special brake prevents accidental release of the head. Cable holder and drill bit storage depot. The head can be rotated 360° on the column.				
Overall height	550mm	2 608 180 002	70.09	82.36 AT
Free overhang	140mm			
Base plate	200 x 200mm			
Clamping diameter	43mm			
Weight	7.0kg			
Industrial Drill Stand for GBM 16-2E, GSB 90-2E + all drills with 43mm collar				
With adjustable stop for adjusting the drilling depth				
Overall height	708mm	0 601 999 015	149.35†	175.49 NT
Free overhang	140mm			
Working stroke	108mm			
Base plate	195 x 195mm			
Weight	16.8kg			
Clamping set for 1119/GBM 16-2E/RE		1 607 000 201	49.76	53.47 AS
Clamping set for 1102		1 607 000 203	48.99	55.21 AS
Set for all 43mm collar drills		1 607 000 202	55.67	65.41 AS
Industrial Drill Stand for GBM 23-2, GBM 23-2E NLA				
With rack guide adjustable working depth				
Overall height	700mm	0 601 999 010	278.31†	327.01 NT
Free overhang	165mm			
Working stroke	120mm			
Base plate	205 x 255mm			
Slot spacing	140mm			
Weight	21kg			
Industrial Drill Stand for 1174				
With adjustable drill depth				
Overall height	700mm	0 601 999 001	154.50	181.54 NT
Maximum clearance	150mm			
Working stroke	115mm			
Base plate	200 x 200mm			
Longhole distance	140mm			
Weight	12.7kg			
Please note: Our drill stands are supplied without chuck guard!				
† Suggested selling price				

OTHER DRILLING ACCESSORIES

Description	Dimensions	Part Number	Ex VAT	Ex VAT
S41 Drill Bit Sharpener				
Sharpens all HSS Metal Drill Bits Accurate 118° Angle. Fits all Drills with 43mm collar diameter (Replacement stone 2 608 600 029 £10.57)	25-10mm	2 607 990 050	30.06	35.32 AT
Replacement stone S40 drill bit sharpener		1 608 600 210	3.02	3.55 AG
DS18 NEW				
Lathe X2. Turns any drill with a 43mm collar and 1/2 x 20 uni chuck mounting thread > 620 watts into an effective lathe. Double guide rails, 150mm sanding plate and 3 pronged star drive.		2 608 190 034	Price & Delivery - on application	
DS18 Accessories				
Gauge 8-10 mm		1 607 959 002	9.57	11.24 AG
Angle Drilling Head: Industrial (use with Chuck 1 608 571 068)		1 608 580 011	191.73	225.28 NT
Gauge 12-14 mm		1 607 959 003	8.39	9.26 AG
Chisel		1 607 959 001	6.08	7.12 AG
Sanding Disc (10 assorted)		1 609 200 171	3.78	4.44 AG
S32				
Angle Head (Use with S51)		0 603 090 000	67.13	78.88 AT
S51				
Spanner Set		0 603 093 000	5.63	6.62 AT
BW13				
Flexible Drive		0 603 091 101	43.69	51.36 AT
S48				
Bench Stand		2 608 120 004	13.06	15.35 AT
S8				
Routing Bench (Used with drill stand BS7 and POW 500A)		0 603 999 002	59.61	70.04 AT
Auxiliary handle		1 612 025 024	8.83	10.38 AS
Depth Stop				
Metal for auxiliary handle 1 612 025 024		1 613 001 005	1.09	1.28 AS
Drilling Angle Controller				
For right angled holes or with angle control up to 15°		1 608 190 006	19.71	23.16 AS
Stirring Attachments				
High volume paint stirrer for chuck mount		1 609 200 251	3.34	3.92 AG
Stirring basket dia. 140 mm, length 595 mm for GRW 11E		3 609 201 036	78.03	91.69 AS
Stirring attachment for GRW11E 120mm x 595mm		2 607 990 016	46.75	54.93 AS
Stirring attachment for GRW11E 160mm x 595mm		2 607 990 017	58.75	69.03 AS
Adaptor 1/2" x M14 for GRW 11E (215 mm long)		3 609 201 037	10.38	12.20 AS
* Fits all drills with handle 1 612 025 024 or handle incorporating 11mm hex hole for depth stop.				
† Suggested selling price				

MAGNETIC STANDS

ROTOMAG 01142 911 020.

DRILLING

Drill Stands and Machine Vices

Attachments

Att
Vanessa
Drummond