







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	05/04/01	MCCORMICK
B	ECN# 1313 PRODUCT VALIDATION	02/27/03	DFP
C	ECN#1605 ADDED COMPONENT SPECIFICATION TABLE	12/10/03	MCCORMICK
D	ECN#2082: CORRECTING LENGTH DIM.	05/24/05	M.LAHEY



RECOMMENDED
PANEL CUT OUT



Component Specifications	
Material	
Housing	ABS 94V-0 Rating
Connector	Plastic; PBT with Glass Fiber
Contact	Brass
Shell	Brass
PCB	Epoxy Glass FP-4 94V-0 Rating
Finish	
Housing	Color; Black
Contact	Gold 30 Micro Inch
Shell	Nickel
Electrical	
Current Rating	2 AMP Max
Voltage Rating	140 VDC
Environmental	
Operating Temperature	-20°C to +80°C

CS-134

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
X ±.1
XX ±.05
XXX ±.005
CABLE LENGTH TOLERANCE
<300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	05/04/2001
CHECKED BY D.PARHAM	05/04/2001
APPROVED BY R.CARRICK	05/04/2001

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION			
USB A-B COUPLER, BLACK			
DRAWING TITLE			
OUTLINE DRAWING			
SIZE	FSCM NO.	DWG. NO.	REV.
A	43321	ECF504B-UAB-OD1	D
SCALE: NONE		CAD FILE: ECF504B-UAB-OD1.SLDDRW	SHEET 1 OF 1