





**Model 7283 & 7284
3-Pin In-Line XLR, Silver Contacts, Nickel Finish****Model 7283, 3-Pin (M) In-Line XLR, Silver Contacts, Nickel Finish****Model 7284, 3-Pin (F) In-Line XLR, Silver Contacts, Nickel Finish****Features**

- 3-Pin XLR Plug (7283) and Jack (7284).
- Streamlined profile with compact shell.
- Handles 14 AWG (2.0mm² Max.).
- Low contact Resistance.
- Solderable.

Materials

- *Body*: Die Cast Zinc Alloy with Tarnish Resistant Nickel Finish
- *Contacts*: Silver Plated Brass
- *Strain Relief*: Clamp designed for durability; POM (Polyoxymethylene).

Specifications

Number of Contacts	3
Contact Resistance	≤ 3 mΩ
Dielectric Strength	1500 Vdc
AWG	14 AWG / 2.5mm ² Max.
Pull Strength	45 lbs.
Cable O.D. Range	3.0mm - 6.5mm (0.118" to 0.255")

Ordering Information

Model: 7283, 7284

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.