

## Cable duct - CD 80X80 WH - 3240635

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable duct, white, comprising upper part and mounting base, width: 80 mm, height: 80 mm, length: 2000 mm

### Product Features

- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Predetermined breaking point enables tool-free, burr-free removal of bars
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool



### Key commercial data

Packing unit	1 pc
Minimum order quantity	6 pc
Weight per Piece (excluding packing)	33.33 GRM
Custom tariff number	39259020
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	2000 mm
Height	80 mm
Width (a)	80 mm

#### Ambient conditions

Ambient temperature (operation)	-5 °C ... 60 °C
---------------------------------	-----------------

#### General

Color	white
-------	-------

## Cable duct - CD 80X80 WH - 3240635

### Technical data

#### General

Components	Lead-free
Inflammability class according to UL 94	V0
Material	PVC

### Classifications

#### eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703

#### ETIM

ETIM 4.0	EC000012
ETIM 5.0	EC000012

#### UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815
UNSPSC 12.01	30101815
UNSPSC 13.2	30101815

### Approvals

#### Approvals

---

#### Approvals

CSA / UL Recognized / VDE Zeichengenehmigung

---

#### Ex Approvals

---

#### Approvals submitted

---

## Cable duct - CD 80X80 WH - 3240635

### Approvals

---

#### Approval details

CSA 

UL Recognized 

VDE Zeichengenehmigung 

### Accessories

#### Accessories

#### Cover

Cover profile - CD COVER 80 WH - 3240649



Cover for cable duct, white, width: 25 mm, length: 2000 mm

---

#### Filler plug

Fastening clip - RVT-PA 4 - 3240498



Plastic body-bound rivet, for hole diameter of 4 mm and a material thickness of 1.5 ... 6 mm

## Cable duct - CD 80X80 WH - 3240635

### Accessories

Fastening clip - RVT-PA 6 - 3240499



Plastic body-bound rivet, for hole diameter of 6 mm and a material thickness of 1.5 ... 6 mm

---

### Riveting tools

Tool - UNIFOX-RVT P 4 - 1212478



Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets

---

Tool - UNIFOX-RVT P 6 - 1212509



Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets

---

### Wiring duct

Universal wire retaining clip - CD WR - 3240284




Universal wire holding bracket, perforated, for wiring channels

---

### Drawings

## Cable duct - CD 80X80 WH - 3240635

Dimensioned drawing



Base perforation according to DIN EN 50085