


Capacitor, film, 0.1 uF, +/-20% Tol, -40/+85C, RC(x2), 630V@85C,  
 Lead Spacing=20.3 mm



### Dimensions (mm)

ID	Dimension	Tolerance
L	24	max
H	14	max
T	7.6	max
S	20.3	+/-0.4
LL	30	nom
F	0.8	nom

### Specifications

Manufacturer:	KEMET
Brand:	Rifa
Capacitance:	0.1 uF
Temperature Range:	-40/+85C
Rated Temperature:	85C
Voltage @ rated temp:	630V
Voltage AC:	250VAC
Tolerance:	+/-20%
Body Type:	Radial Molded
Construction:	Wound
Application:	RC(x2)
Electrical Name (Other):	Resistor
Electrical Value (Other):	100
Electrical Units (Other):	Ohms
Insulation Resistance:	3 GOhm
UL_1283:	250V
IEC_60384-14:	250V
Miscellaneous Electrical:	PMR209
Package Kind:	Bulk
Package Quantity:	250

#### Notes:

-Capacitor and Resistor are in series inside of case

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kemet:

[PMR209MC6100M100R300PS](#)