


Plastic Boxes

Utilibox Style L



[Click on Image for Larger View](#)

Bud Utilibox is the ultimate value in plastic utility boxes. Now available in a variety of styles and sizes. Contact BUD factory for optional colors, material, EMI/RFI shielding and custom modification.

Design Features

- Flame retardant ABS plastic with UL 94V-O flammability rating. Suggested service temperature -20 degrees C to +70 degrees C.
- Comes with close fitting interlocking screw-on and assembly hardware.
- Horizontal PCB mounting bosses.
- Molded-in mounting brackets are provided on catalog numbers having -MB suffix.
- Finish: Fine Textured Black -- well suited for silk-screening or pad printing. Special colors available on request.



Utilibox Style L									
Catalog Number	Drawings	External Dimensions (Inches)				Internal Dimensions (Inches)			Weight (Ozs.)
		A	B	C	D	E*	F*	G*	
CU-1931-MB	N/A	3.12"	2.10"	1.08"	1.00"	2.90"	1.90"	.93"	N/A
CU-1933-MB	N/A	3.12"	2.13"	1.58"	1.50"	2.90"	1.90"	1.43"	N/A
CU-1935-MB	N/A	3.11"	3.10"	.95"	.88"	2.90"	2.90"	.79"	N/A
CU-1937-MB	N/A	3.11"	3.13"	1.56"	1.49"	2.90"	2.90"	1.40"	N/A
* Reference only - Request drawing for internal configuration and dimensions. N/A -- Contact factory.									