

181-23005

Slotted Wall Wiring Duct, 2" X 3", Non-Adhesive, PVC, Gray, 30ft/Box

Article Number: 181-23005

Part Number: 181-23005

Type: SL2X3

[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)

[!\[\]\(3342c215b2a8b663596a81468d5dc314_img.jpg\) \[!\\[\\]\\(5e22d44aef1f9548ca8274cbfb388e9d_img.jpg\\) \\[!\\\[\\\]\\\(b011182daf5a0527ed818f91dc4cf8f7_img.jpg\\\) \\\[!\\\\[\\\\]\\\\(e021942709a217cfed2f781c62feb09c_img.jpg\\\\) | \\\\[!\\\\\[\\\\\]\\\\\(189fbc627457efb1015bb006253636f9_img.jpg\\\\\) Share\\\\]\\\\(#\\\\)\\\]\\\(#\\\)\\]\\(#\\)\]\(#\)](#)

Base Data

Part No.	181-23005
Type	SL2X3
Color	Gray (GY)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Product Dimensions

Length (L)	6.0ft / 1.83m
Width (W) (imperial)	2.02"
Width (W)	51.31mm
Width (W2)	2.0" / 50.8mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	2.6" / 66.0mm
Width (W6)	0.5" / 12.7mm
Height (H)	3.0" / 76.2mm
Mounting Hole Centers	4.00" / 101.6mm

Material and Specifications

Material	Polyvinylchloride (PVC)
CSA Certified	Yes
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	CSA / UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes / Yes

Logistic and Packaging

Packaging Type	box
Pkg. Qty.	30 / 9.14m
Carton Qty.	120
UPC	089306293194

Find a Distributor

Get Product Samples

Get Technical Drawings