






DG301-5.0



APPROVAL

Electrical

Standard

Rated voltage

Rated current

Wire range

Withstanding voltage



UL

300V

15A

22-14AWG

IEC

250V

17.5A

1.5mm²

AC2000V/1Min

Mechanical

Torque

Ambient temperature

Strip length

Dimensions

Pitch

Poles

0.4Nm(3.5Lb-In)

-30°C~+120 °C

5-6mm

5.0mm(.197")

2P,3P-24P

Material

Housing

Screws

Pin header

Wire guard

PBT,UL94V-0


M2.5,Steel, Cr³⁺ Zn-plated

Brass,Tin-plated

Stainless steel

HOW TO ORDER :

	-		P	-	1		-	X	X	X
								Customer Request		
Series number	No.of pole	Color		1 Single pitch		2 Double pitch				
		1 Grey	4 Green	7 Trans Parent	2 Blue	5 Orange	8 Yellow	3 Black	6 Red	9 White



DEGSON ELECTRONICS CO., LTD.

NAME

DG301-5.0