

[Home](#) - [Distributor Area](#) - [Distributors](#) - [Support](#) - [Jobs](#) - [Contact](#)Choose your language: [English \(US\)](#) 

Search Product:

[\[ Advanced \]](#)

- [Adapters & power supplies](#)
- [Batteries & chargers](#)
- [Cables & accessories](#)
- [Connectors](#)
- [Consumer products & pc acc.](#)
- [Electronic components](#)
- [High-q tools & dmm's](#)
- [Led products & lamps](#)
- [Light products](#)
- [Loudspeakers & pa systems](#)
- [Perel tools](#)
- [Security products](#)
- [Velleman kits & oscilloscopes](#)

[ELECTRONIC COMPONENTS](#) > [BUZZERS & SIRENS](#) > [BUZZERS](#) > [PANEL-MOUNTED BUZZERS](#)

&gt;



## PANEL-MOUNTING BUZZER 4-28V DC / 8mA PCB TYPE

Order Code: SV5



### Features



[ROHS Info](#)

- panel-mounting type with screw connectors
- continuous or pulse mode
- high sound pressure level
- operating power: 4-28V DC / 8mA

### Specifications

- tone type: single / pulse
- operating voltage: 3 - 28V DC
- rated voltage: 12V DC
- current consumption: 8mA
- osc. frequency: 3.5kHz
- sound level: 90dB
- connector type: screw
- body color: gray
- weight: 0.77oz

[More...](#)

### Stock Info

- Inner carton: 50

- Outer Carton: 500
- EAN Barcode: 5410329238896
- Packaging: Bulk

(C) 2005 Velleman Components N.V.  
[ [Disclaimer](#) ]