


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE (SQUARE WAVE)	10	Vp-p
OPERATING VOLTAGE RANGE	5 ~ 24	Vp-p
RATED CURRENT (MAX)	10	mA
CAPACITANCE	25,000±30%	pF
MINIMUM SPL @ 10 CM	90	dBA
RESONANT FREQUENCY	3,200±500	Hz
OPERATING TEMPERATURE	-30 ~ +115	°C
STORAGE TEMPERATURE	-40 ~ +125	°C
HOUSING MATERIAL	MPPO+GLASS	-
TERMINAL MATERIAL	RED COPPER	-
WEIGHT	3.7	grams


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	9/17/03	
A	REVISED TO NEW TEMPLATE	6/16/04	R. W.



NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AT-531.DWG

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS. TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.				projects® unlimited		Dayton , Ohio	
		TRANSDUCER(ELECTRO-MECH) AT-531					
		APPROVALS		DATE			
DRAWN		R. A. C.		9/03			
APPROVED		R. W.		9/03			
DO NOT SCALE DRAWING		SIZE A		DRAWING NO. AT-531			
		SCALE: N.T.S.				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-531](#)