



Clipper Industrial Plastic Connectors



Machined contacts

Packaging	Contact types		Part numbers	Size	Ø mm over insulation (inches)	AWG	Admissible section mm2
Bulk	crimp	male	CM16PC10MQ	16	2 mm to 3 mm (0.08" to 0.12")	18 to 14	0.93 to 1.91 mm ²
		female	CM16SC10MQ				
	solder	male	CM16PS10MQ			14* Max	
		female	CM16SS10MQ				
	crimp	male	CM10PC10MQ	20	1.2 mm to 2.1 mm (0.05" to 0.08")	24 to 18	0.21 to 0.93 mm ²
		female	CM10SC10MQ				
	solder	male	CM10PS10MQ			18 Max	
		female	CM10SS10MQ				
	crimp	male	CM16PC00MQ	16	2 mm to 3 mm (0.08" to 0.12")	18 to 13	0.93 to 2.60 mm ²
		female	CM16SC00MQ				
 contact reducing sleeve cable		male	CM16PC20MQ	16	2 to 3 mm (0.08" to 0.12")	20	0.21 to 0.60 mm ²
		female	CM16SC20MQ				
		male	CM10PC20MQ	20	1.2 to 2.1 mm (0.05" to 0.08")	30 to 24	0.06 to 0.21 mm ²
		female	CM10SC20MQ				
Plating MQ : 0.4µ mm gold on active part (.016µ inches)							
* Up to 1.91 mm ²							

Extended ground contact-crimp (Length + .039 inch = +1 mm)

Bulk		male	16	0.08" to 0.12"	18 to 14	8501 9641
		male	20	0.05" to 0.08"	24 to 18	8501 9642 CL