

Piezo Buzzer

EFM-250




FEATURES:

- SMT Inside
- Sealed Type for Wave Soldering
- Small Size

APPLICATIONS:

- Automatic Control Equipment
- Communication Equipment
- Electronic Instruments

DIMENSIONS: (Unit: mm)



ELECTRICAL SPECIFICATIONS:

Min. Sound Pressure Level at

12V_{DC} / 10cm 5dB(A)

Rated Voltage 12V_{DC}

Operating Voltage 6~16V_{DC}

Max. Consumption 8mA/12V_{DC}

Oscillating Frequency 4.0 ~ 0.5 kHz

Tone Nature Continuous

Operating Temperature -25~+85℃

Storage Temperature -25~+85℃

Case Material/Color ...PC/Black

Weight 1g

PACKING INFORMATION:

Packing: 6000 pcs per export carton

Carton Size 5×475 cm

G. Weight: 8 kgs N. Weight: 6.5 kgs

Address: No. 12. Lane 722. Sangtian Road Jiangdong Science Garden

Ningbo, 315040 P. R. China

Fax No: (0574)87803761

Tel: (0574)87802511

