



# Build a top quality maintenance toolkit without paying top brand prices.

Get professional products for better value, with our branded range.



Professionally approved products.

[www.rs-components.com](http://www.rs-components.com)

# The new generation of RS Brand tools for Maintainers and Electricians

**With RS branded products you get:**

- Savings of up to 30% on leading manufacturer brands
- Competitive pricing with no compromise on quality
- Tried and tested products

**3**      **MULTI TOOLS**



**6**      **UTILITY KNIVES**



**10**      **HAMMERS**



**13**      **HACKSAWS**



**17**      **SCREWDRIVERS**



**20**      **LUBRICATION**



**27**      **TECH CASES**



**30**      **TOOL STORAGE**



**34**      **INSPECTION CAMERA**



# MULTI TOOLS

## 11 IN 1 MULTI TOOL WITH LED FLASHLIGHT

- Stainless steel construction
- Includes canvas pouch



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4625 | 130 x 65 x 30 | 0.29 |



# MULTI TOOLS

## 15 IN 1 MULTI TOOL

- Aluminium construction
- Includes canvas pouch



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4613 | 130 x 65 x 30 | 0.27 |

## 8 IN 1 MULTI FUNCTION TOOL

- Stainless steel construction
- Includes canvas pouch



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4631 | 130 x 65 x 30 | 0.18 |



# MULTI TOOLS

## ELECTRICIANS MULTI TOOL

- Stainless steel construction, with rubber inlays for added grip
- Includes canvas pouch



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4629 | 130 x 65 x 30 | 0.23 |

## 8 IN 1 MULTI FUNCTION SNIPS

- Stainless steel construction, with rubber inlays for added grip
- Includes canvas pouch



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4638 | 130 x 65 x 30 | 0.23 |



# UTILITY KNIVES

## RETRACTABLE QUICK CHANGE KNIFE

- Heavy duty zinc alloy construction
- Auto loading function
- Easy access blade compartment
- Contoured non slip grip
- Accepts industry standard blades

- Auto loading function

- Easy access blade compartment

- Heavy duty zinc alloy construction

- Contoured non slip grip



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4619 | 165 x 45 x 25 | 0.26 |



# UTILITY KNIVES

## FIXED UTILITY KNIFE

- Heavy duty zinc alloy construction
- Twist to open
- Contoured non slip grip
- Accepts industry standard blades

**HeavyDuty**



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4603 | 155 x 35 x 25 | 0.19 |



## RETRACTABLE UTILITY KNIFE

- Heavy duty zinc alloy construction
- Switch to open
- Contoured non slip grip
- Accepts industry standard blades

**HeavyDuty**



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4616 | 165 x 40 x 25 | 0.22 |



# UTILITY KNIVES

## SAFETY KNIFE

- Heavy duty zinc alloy construction
- Automatic blade retraction
- Contoured non slip grip
- Ergonomic thumb control

**HeavyDuty**



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4607 | 150 x 40 x 25 | 0.08 |

## LOCK BACK KNIFE

- Lock-back blade
- Quick blade change mechanism
- Lock out blade function
- Aluminum body, with release switch
- Accepts industry standard blades



| CODE NO  | HxWxD / mm   | kg   |
|----------|--------------|------|
| 789-4596 | 80 x 30 x 18 | 0.08 |



# UTILITY KNIVES

## 9MM SNAP OFF KNIFE

- Positive blade auto-lock
- Stores 2 blades
- ABS body with TPR soft grips



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4590 | 140 x 30 x 25 | 0.04 |

## 18MM SNAP OFF KNIFE

- Positive blade auto-lock
- Stores 2 blades
- ABS body with TPR soft grips



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4600 | 160 x 48 x 25 | 0.07 |



# HAMMERS

- Steel locking plate - eliminates head getting loose or falling apart


- Drop forge head - with striking ends induction hardened 52-56 hrc

- Spring steel bars - 9/32" (7.1 Mm) dia. Spring steel bars resist overstrike without breaking

- Steel reinforced lanyard hole

- Hi visibility head - adds instant identification on any job site

- Vulcanized rubber grip - absorbs impact & vibration reducing user fatigue. Protects user in the event of striking an electrical wire. Made from special grade of ozone resistant rubber for use in tough outside environments. Handles on most head sizes weigh more than the head, allowing user to apply double the torque



# HAMMERS

## 12" INDESTRUCTIBLE CLUB HAMMER - 2.5LB & 4LB

- Revolutionary indestructible handles constructed from spring steel eliminates any overstrike breakage
- Steel locking plates ensures head will not detach from the handle
- Induction hardened striking faces (52-56 HRC)
- Fully coated rubberised handle absorbs impact & vibrations reducing user fatigue. Non perishing material extends life in any condition.



| CODE NO  | Handle / mm | Head Weight<br>kg |
|----------|-------------|-------------------|
| 790-4710 | 300         | 1.1               |
| 790-4729 | 300         | 1.8               |



## 16" INDESTRUCTIBLE CROSS PEIN HAMMER - 2LB & 3LB

- Revolutionary indestructible handles constructed from spring steel eliminates any overstrike breakage
- Steel locking plates ensures head will not detach from the handle
- Induction hardened striking faces (52-56 HRC)
- Fully coated rubberised handle absorbs impact & vibrations reducing user fatigue. Non perishing material extends life in any condition.



| CODE NO  | Handle / mm | Head Weight<br>kg |
|----------|-------------|-------------------|
| 790-4722 | 400         | 0.9               |
| 790-4726 | 400         | 1.4               |



# HAMMERS

## 14" INDESTRUCTIBLE BALL PEIN HAMMER - 240Z & 320Z

- Revolutionary indestructible handles constructed from spring steel eliminates any overstrike breakage
- Steel locking plates ensures head will not detach from the handle
- Induction hardened striking faces (52-56 HRC)
- Fully coated rubberised handle absorbs impact & vibrations reducing user fatigue. Non perishing material extends life in any condition.



| CODE NO  | Handle / mm | Head Weight<br> Kg |
|----------|-------------|-----------------------------------------------------------------------------------------------------|
| 790-4735 | 350         | 0.7                                                                                                 |
| 790-4738 | 350         | 0.9                                                                                                 |



# HACKSAWS

## 12" HEAVY DUTY PRO HACKSAW

- Heavy duty tubular frame
- High tension blade
- Soft grip handles at front and butt
- 32tpi bi-metal blade

**HeavyDuty**

- Soft grip handle

- Heavy duty tubular frame

- 32tpi bi-metal blade

- High tension blade

- Soft grip handle



| CODE NO  | HxWxD / mm     | kg   |
|----------|----------------|------|
| 789-4584 | 410 x 135 x 28 | 0.64 |



# HACKSAWS

## 12" & 6" HACKSAW TWINPACK

- 6" jr hacksaw with 24tpi carbon steel blade
- 12" Hacksaw with 32tpi bi-metal blade
- 12" Hacksaw features a reversible spine to converts to close quarters saw
- 12" Hacksaw features dual position blade mounts (0 & 45 deg)
- Ergonomic Designs with comfort grips



| CODE NO  | HxWxD / mm     | kg   | HxWxD / mm    | kg   |
|----------|----------------|------|---------------|------|
| 789-4593 | 405 x 140 x 30 | 0.48 | 255 x 95 x 25 | 0.19 |



# HACKSAWS

## ADJUSTABLE HACKSAW 300MM / 250MM

- Accepts 250 & 300mm blades
- Quick adjustable frame
- High tension blade
- 32tpi bi-metal blade



| CODE NO  | HxWxD / mm     | kg   |
|----------|----------------|------|
| 789-4580 | 450 x 120 x 18 | 0.29 |



## CLOSE QUARTERS HACKSAW

- Aluminium alloy frame, with ergonomic rubber handles
- For use in hard to access areas
- Accepts 10" blades
- Quick release blade mechanism
- Supplied with 24tpi HSS blade



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4587 | 280 x 70 x 25 | 0.16 |



# HACKSAWS

## 6" JR HACKSAW

- Balanced frame
- Ergonomic handle
- High tension blade
- 24tpi carbon steel blade




| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 789-4578 | 255 x 95 x 20 | 0.11 |



## 6" WIRE FRAME JR HACKSAW

- Polished nickel frame
- 24tpi carbon steel blade



| CODE NO  | HxWxD / mm   | kg   |
|----------|--------------|------|
| 789-4574 | 235 x 65 x 5 | 0.07 |



# SCREWDRIVERS

- Palm saver cap

- Patented pull out retracting cartridge design

- Handle is made from ABS resin

- Easy guide collar

- Alloy steel shaft

- Diameter 1-3/8" (35mm)



# SCREWDRIVERS

## 15 IN 1 INTERCHANGEABLE SCREWDRIVER

- All purpose bit load driver loaded with 7 double end professional quality bits
- Magnetic bit holder. End of Shaft is a 1/4" hex nut driver
- Retractable Bit Cartridge - Makes it easy to find, store and change bits
- Specially designed Palm Saver Cap prevents blisters in the palm of your hand. Cap does not turn as you push on the cap and turn the handle
- Easy Guide Collar provides greater control by maintaining full contact between the bit and the screw
- Specially Engineered ABS resin handle
- Industrial grade S2 modified Steel bits with Rockwell hardness 58 - 62
- Phillips 0-3, Pozzi 1-2, Slotted 4-6, Hex 1/8" - 5/32", Torx 10-30




| CODE NO  | HxW / mm | kg   |
|----------|----------|------|
| 790-4700 | 225 x 40 | 0.23 |



## INTERCHANGEABLE TAMPER PROOF SCREWDRIVER

- Must for all commercial/industrial tradesmen i.e. electricians, locksmiths, telephone technicians, maintenance personnel, etc
- Magnetic bit holder. End of Shaft is a 1/4" hex nut driver
- Retractable Bit Cartridge - Makes it easy to find, store and change bits
- Specially designed Palm Saver Cap prevents blisters in the palm of your hand. Cap does not turn as you push on the cap and turn the handle
- Easy Guide Collar provides greater control by maintaining full contact between the bit and the screw
- Specially Engineered ABS resin handle
- Industrial grade S2 modified Steel bits with Rockwell hardness 58 - 62
- Hex pin 1/8", 9/64", 5/32", 3/16", Spanner 6-12, Torq pin 10-30



| CODE NO  | HxW / mm | kg   |
|----------|----------|------|
| 790-4713 | 225 x 40 | 0.23 |



# SCREWDRIVERS

## RATCHETING INTERCHANGEABLE SCREWDRIVER

- Features ZAD 8 Zinc Alloy SOLID-CORE ratchet that delivers over 25 Nm of torque strength. Precision 28 Tooth ratchet design makes driving fasteners faster and easier
- Magnetic bit holder. End of Shaft is a 1/4" hex nut driver
- Retractable Bit Cartridge - Makes it easy to find, store and change bits
- Specially designed Palm Saver Cap prevents blisters in the palm of your hand. Cap does not turn as you push on the cap and turn the handle
- Easy Guide Collar provides greater control by maintaining full contact between the bit and the screw
- Specially Engineered ABS resin handle
- Industrial grade S2 modified Steel bits with Rockwell hardness 58 - 62
- Phillips 0-3, Pozi 1-2, Slotted 4-6, Torx 10-25



| CODE NO  | HxW / mm | kg   |
|----------|----------|------|
| 790-4716 | 225 x 40 | 0.23 |



# LUBRICATION

- Heavy Duty aluminum die cast head with precision honed bore for rapid action

- Head casting fitting with bulk loader valve

- Ergonomic pistol grip and acute angle design - for ease of operation in narrow spaces

- Cartridge, Suction or filler pump loading



## AIR OPERATED GREASE GUN

- All metal construction, fully CNC machined with hardened wear resistant moving parts
- Strainer at the suction tube inlet prevents contaminants from entering the system
- Virtually soundless pump. Noise level of 81 db only
- Air Inlet connection: 1/4" BSP (F), Pump Outlet: 1/4" BSP (F), Grease Output: 1.10 kg / minute
- Air hose length: 2160 mm
- Complete with adjustable drum trolley. Suitable for drum up to 60L capacity, Steel construction with HD Wheels



| CODE NO  | HxW / mm   | Barrel  | kg |
|----------|------------|---------|----|
| 786-5261 | 1000 x 445 | 12.5 Kg | 14 |
| 786-5270 | 1000 x 445 | 50 Kg   | 14 |



## AIR OPERATED GREASE GUN 4,800 PSI

- Heavy Duty aluminum die cast head with precision honed bore for rapid action
- Ergonomic pistol grip and acute angle design - for ease of operation in narrow spaces
- Head casting fitting with bulk loader valve
- Cartridge, Suction or filler pump loading
- Intermittent Action with grease discharge per shot, Air Operating Range: - 40-120 PSI, Pressure Ratio - 40:1"



| CODE NO  | HxWxD / mm     | kg  |
|----------|----------------|-----|
| 786-5309 | 410 x 180 x 65 | 1.8 |



## HEAVY DUTY GREASE GUN 10,000 PSI

- Heavy Duty Aluminum die cast head with bulk loader & air release valve, Rugged and robust Zinc plated handle
- Delivers 1gm/stroke
- Variable stroke feature allows convenient usage even in confined areas
- Cartridge, Suction or filler pump loading
- Complete with 150 mm bent steel extension & 4 jaw coupler



| CODE NO  | HxWxD / mm     | kg  |
|----------|----------------|-----|
| 786-5283 | 380 x 127 x 60 | 1.5 |



## STANDARD DUTY GREASE GUN 6,000 PSI

- Steel Head
- Soft rubber grip for ease of use
- Most Popular gun for general purpose lubrication, Delivers 1gm/stroke
- Complete with 150 mm bent steel extension & 4 jaw coupler
- Cartridge, Suction or filler pump loading



| CODE NO  | HxWxD / mm     | kg   |
|----------|----------------|------|
| 786-5277 | 380 x 127 x 60 | 1.38 |



## PISTOL HANDLE GREASE GUN 5,000 PSI

- Pistol handle designed to prevent fingers from "Pinching"
- Delivers 0.5gm/stroke
- Complete with 100 mm straight steel extension & 4 jaw coupler
- Cartridge & Suction Fill



| CODE NO  | HxWxD / mm     | kg  |
|----------|----------------|-----|
| 786-5289 | 366 x 131 x 35 | 1.3 |



## MINI PISTOL GREASE GUN 3,500 PSI

- One Hand Pistol type tool box size Gun, in a textured zinc plated finish
- Convenient pull type operating mechanism
- Delivers 0.40gm/stroke
- Complete with 100 mm straight steel extension & 4 jaw coupler
- Cartridge & Suction Fill



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 786-5273 | 250 x 65 x 65 | 0.55 |

## 500ML SUCTION GUN FLEXSPOUT

- Rugged construction, steel plated head and deluxe lip seal for maximum suction
- Needs no priming
- Suitable for use with non corrosive liquids
- Complete with 300 mm flexible vinyl hose
- Spout length: 310 mm



| CODE NO  | HxWxD / mm    | kg  |
|----------|---------------|-----|
| 786-5299 | 335 x 65 x 65 | 0.9 |



## PUSH GREASE GUN 30CC

- Push type grease gun for use with bulk grease only
- Compact toolbox size, ideal for greasing impact wrenches, lawn mowers, chain saws, trailers, ATV's, autos & trucks etc
- 1000psi
- Comes complete with universal connector
- Can be custom built with pointed nozzle for special applications



| CODE NO  | HxWxD / mm    | kg   |
|----------|---------------|------|
| 786-5292 | 165 x 43 x 43 | 0.26 |



## PUSH GREASE GUN 125CC

- Push type grease gun for use with bulk grease only
- Compact toolbox size, ideal for greasing impact wrenches, lawn mowers, chain saws, trailers, ATV's, autos & trucks etc
- 1000psi
- Comes complete with universal connector
- Can be custom built with pointed nozzle for special applications



| CODE NO  | HxWxD / mm    | kg  |
|----------|---------------|-----|
| 786-5295 | 210 x 48 x 48 | 0.4 |



**786-5286**

## **GREASE GUN ACCESSORY KIT**

- Kit comprising of most popularly used greasing couplers
- Standard 4 jaw coupler (3500psi)
- Professional 3 jaw coupler (6000psi)
- Professional 4 jaw coupler (6000psi)
- Hook on coupler (3000psi)
- Push on coupler (3000psi)



**786-5302**

## **GREASE GUN COUPLER & NOZZLE KIT**

- Kit comprising of most popularly used greasing nozzles
- 6" rigid angled
- 12" Flexi
- 18" Flexi
- 3,500psi working pressure, 11,600psi bursting pressure
- Thermoplastic hose with outer diameter of 8.5mm
- Highly flexible with a minimum bending radius of 40mm



- IP67 Rated

- Completely dust tight

- Water tight to 1m Submersion



## BLACK IP67 CASE WITH FOAM 240X195X112MM

- 9" IP Rated Technicians case with foam insert
- 240 x 195 x 112mm
- IP67 Rated
- Completely dust tight
- Water tight to 1m Submersion




| CODE NO  | HxWxD / mm      | kg    |
|----------|-----------------|-------|
| 788-7236 | 240 x 195 x 112 | 0.765 |



## BLACK IP67 CASE WITH FOAM 420X325X175MM

- 16.5" IP Rated Technicians case with foam insert
- 420 x 325 x 175mm
- IP67 Rated
- Completely dust tight
- Water tight to 1m Submersion




| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7239 | 420 x 325 x 175 | 2.69 |



# TECH CASES

## BLACK IP67 CASE WITH FOAM 465X360X175MM

- 18" IP Rated Technicians case with foam insert
- 465 x 360 x 175mm
- IP67 Rated
- Completely dust tight
- Water tight to 1m Submersion



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7233 | 465 x 360 x 175 | 2.90 |

## BLACK IP67 CASE WITH FOAM 515X435X225MM

- 20.5" IP Rated Technicians case with foam insert
- 515 x 435 x 225mm
- IP67 Rated
- Completely dust tight
- Water tight to 1m Submersion



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7242 | 515 x 435 x 225 | 5.11 |



# TOOL STORAGE

## ELECTRICIANS TOOL BAG WORKSTATION

- Constructed from tough padded tear resistant polyester
- Tri sector workstation with multiple storage options for electricians/engineers/ technicians tools
- Comfortable strap

- Tough, padded, tear resistant polyester

- Multiple storage options

- Comfortable strap



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7223 | 400 x 300 x 170 | 2.35 |



# TOOL STORAGE

## 12" HARD BOTTOM TOOL BAG

- Constructed from tough padded tear resistant polyester
- Durable welded plastic waterproof base
- Multiple pockets
- Padded shoulder strap

**Heavy Duty**



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7205 | 310 x 200 x 210 | 0.99 |



## 16" HARD BOTTOM TOOL BAG

- Constructed from tough padded tear resistant polyester
- Durable welded plastic waterproof base
- Multiple pockets
- Padded shoulder strap

**Heavy Duty**



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7214 | 430 x 240 x 250 | 1.32 |



# TOOL STORAGE

## 16" RUCKSACK

- 16" (406mm) Rucksack with reflective piping
- Double zipped bottom section for laptop or similar
- Multiple pockets
- Drinks holder
- Mobile phone/mp3 player holder on strap



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7211 | 340 x 240 x 410 | 1.88 |

## TOOL BELT WITH HOLSTER & POUCH

- Modular toolbelt comprising of 3 sectors
- Constructed from tough padded tear resistant polyester
- Breathable padded, adjustable belt (90-120cm) with double fastenings for extra comfort and safety
- Drill holster, with secure strap
- Hammer loop & tape measure fixing point
- Multiple compartments for tools/fixings etc



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7217 | 560 x 265 x 100 | 0.40 |



# TOOL STORAGE

## ELECTRICIANS TOOL POUCH

- Tool pouch constructed from tough padded tear resistant polyester
- Tape measure fixing point & Tape holder chain
- Large compartments for easy access
- Breathable padded, adjustable belt (90-120cm) with double fastenings for extra comfort and safety.



| CODE NO  | HxWxD / mm     | kg   |
|----------|----------------|------|
| 788-7220 | 270 x 310 x 40 | 0.30 |



## GENERAL TOOLBELT

- Tool pouch constructed from tough padded tear resistant polyester
- Hammer loop & tape measure fixing point
- "2 Large compartments and 4 pen/screwdriver slots"
- Breathable padded, adjustable belt (90-120cm) with double fastenings for extra comfort and safety.



| CODE NO  | HxWxD / mm      | kg   |
|----------|-----------------|------|
| 788-7227 | 270 x 290 x 100 | 0.65 |



# INSPECTION CAMERA

## DIGITAL INSPECTION CAMERA

- 5.5mm camera and flexi hose
- Takes stills and videos
- 4 x Zoom
- Internal memory and SD card compatible
- A/V output

- Takes stills and videos

- Internal memory and SD card compatible

- A/V output

- 5.5mm camera

- Flexi hose



| CODE NO  | HxWxD / mm     | kg |
|----------|----------------|----|
| 790-3381 | 330 x 220 x 80 | ?  |

