


REV.	DATE	ECR NO.	DESCRIPTION
NC	02/03/09	—	INITIAL RELEASE



LENGTH TABLE	
PART NUMBER	LENGTH (IN.)
135101-02-06.00	6.00
135101-02-12.00	12.00
135101-02-24.00	24.00
135101-02-36.00	36.00

- NOTE:
1. PERFORM CONTINUITY AND HI-POT TESTING.
 2. PACKAGED INDIVIDUALLY IN HEAT SEALED POLY BAG.

3	009-954-341	HEAT SHRINK TUBING, BLACK, 3/16" DIAMETER	A/R FT
2	009-881-159	COAXIAL CABLE, RG174/U	A/R FT
1	132114	CONNECTOR, SMA STRAIGHT PLUG, GOLD	2
	PN	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
	DRAWN	G.R.S.	02/03/09								
	CHECKED				PART DESCRIPTION						
	ISSUED				SMA PLUG TO SMA PLUG, RG174						
	SHEET	1 OF 1			PART NO.						
					135101-02-XX.XX						
	CAD FILE	C:/135/135101-02-XX.XX.DWG		DWG. NO.		135101-02-XX.XX.DWG	REV.	NC	SIZE	A	SCALE