

3M

PTFE Film Tape

5498

Technical Data

Product Description 3M™ PTFE Film Tape 5498 has a film backing with a non-silicone rubber adhesive.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Extruded PTFE (polytetrafluoroethylene)	Rubber	Brown	36 yds. (32.9 m)

Typical Physical Properties **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

ASTM Test Method		
Adhesion to Steel:	48 oz./in. width (53 N/100 mm)	D-3330
Tensile Strength at Break:	19 lbs./in. width (332 N/100 mm)	D-3759
Elongation at Break:	105%	D-3759
Backing Thickness:	2.0 mils (0.05 mm)	D-3652
Total Tape Thickness:	4.0 mils (0.10 mm)	D-3652
Temperature Use Range:	40° to 300°F (4° to 149°C)	

Features

- Withstands autoclave cycles for several hours at temperatures up to 350°F (176°C) and 400°F (204°C) exposure for shorter periods.
- Extruded PTFE film tape lies flatter than typical skived PTFE film tapes.

CAUTION: When PTFE film tape is exposed to temperatures above 600°F (316°C), small quantities of hazardous vapors may be released. INHALATION OF THESE VAPORS MAY BE HARMFUL OR MAY CAUSE RESPIRATORY TRACT IRRITATION. Do not heat or expose PTFE film tape to temperatures above 600°F (316°C).

Application Ideas

- Lining of composite bonding tool frames where there is concern of silicone contamination.
- Masking and bundling of composite parts prior to bonding operations where there is concern of silicone contamination.

3M™ PTFE Film Tape

5498

Storage	Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.
----------------	---

Shelf Life	To obtain best performance, use this product within 18 months from date of manufacture.
-------------------	---

Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
------------------------------	--

Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
--------------------	--

Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
---	---

Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.
--------------------------------	--

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2010 70-0709-5116-8 (8/10)