




1. MARKED PER MIL-STD-130.
2. LEADS WILL MATE WITH AMP LGH-3 RECEPTACLE WITH 1.81 [46.0] BARREL DEPTH.
3. PIGTAIL IS SOLDER DIPPED.
4. OPERATING VOLTAGE: 40 KVDC AT 0 TO 70,000 FEET, -55° C TO 125° C.
5. INSULATION CUT, BUT NOT REMOVED
6. YELLOW WIRE DOES NOT HAVE A SOLID YELLOW INSULATION BUT IS A WHITE WIRE WITH A YELLOW STRIPE.

5	60.00±1.00 [1524.0±25.4]	.67 [17.0]	5-868353-2
3	60.00±1.00 [1524.0±25.4]	.67 [17.0]	868353-2
3	18.00±.12 [457.2±3.0]	.55 [13.8]	868353-1
REMARKS	DIM B	DIM A MIN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 12-15-97 CHK D.EABY 12/15/97 APVD — PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	NAME LEAD ASSY, SGL END, LGH-3 WIRE COLOR: WHITE AND YELLOW STRIPED
DIMENSIONS: INCHES [mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .02 [0.5] 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH SEE CALLOUTS	SIZE A2 CAGE CODE 00779 DRAWING NO. C-868353 SCALE 2:1	RESTRICTED TO — REV C
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	CUSTOMER DRAWING	