



Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
    - PDFMini-Com FJ ..
    - DXFMini-Com FJ ..
    - ZIP-MINCOM FJ ..
    - DWG-Mini-Com FJ ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor
- Install & Maintain
  - Installation Instructions
    - PDFVisual Fault ..
    - PDFMini-Com FJ ..
  - Stripping Templates
    - PDFMini-Com FJ ..

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'FJJSMM5CAW'

Your search criteria matched only one product, shown below

FJJSMM5CAW



- TIA/EIA604 FOCIS-6 compliant connectors
- Exceed TIA/EIA568-B.3 requirements
- Insertion loss: 0.35dB average (50/125  $\mu$ m), 0.3dB average (62.5/125  $\mu$ m)
- Return loss: >20dB
- Pre-polished mechanical crimp termination eliminates polishing and adhesive, reducing installation time by 70% over field polish FJ <sup>®</sup> Jack Modules
- Non-optical disconnect maintains data transmission under tensile loads for jacketed cable
- Mechanical crimp cable retention consistently provides higher than industry standard cable retention
- RJ45 small form factor duplex jack module – double the port density in one module space
- *Mini-Com* <sup>®</sup> Jack Modules snap in and out of all *Mini-Com* <sup>®</sup> telecommunications room products and work area outlets
- Each duplex jack module includes housing, cover, two ferrule assemblies with pre-polished fiber stubs, two crimp sleeves, one boot for 900  $\mu$ m buffered fiber, one boot for 3mm jacketed

cable, and one dust cap

- Can be clearly identified with labels and icons
- Fiber cable type: tight-buffered only
- Fiber cable size: 900  $\mu$ m tight-buffered fiber or 3.0mm jacketed cable
- For 250 $\mu$ m coated fiber termination, use 250 micron fiber build-up tube kit or fan-out kits
- Ferrule type: 2.5mm zirconia ceramic (highest durability for repeated matings)
- FJ<sup>®</sup> *Opti-Crimp* <sup>®</sup> Jack Modules and crimp tool allow visual verification of optimal continuity during crimp termination with the FVFLY visual fault locator and FVFLPCY patch cord (included in FJMVKIT termination kit)
- Use *Opti-Crimp* <sup>®</sup> Termination Kit (FJMVKIT)

|                              |                                                                                                                                                                                                                        |
|------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part Number                  | FJJSMM5CAW                                                                                                                                                                                                             |
| RoHS Compliancy Status       | Compliant                                                                                                                                                                                                              |
| Part Description             | FJ <sup>®</sup> <i>Opti-Crimp</i> <sup>®</sup> 62.5/125 $\mu$ m Multimode Duplex Fiber Optic Jack Module with phosphor bronze split sleeves for 3.0mm jacketed cable or 900 $\mu$ m tight-buffered fiber installation. |
| Product Type                 | FJ <sup>®</sup> Jack Modules                                                                                                                                                                                           |
| Color                        | Arctic White                                                                                                                                                                                                           |
| Fiber Compatibility          | 62.5/125 $\mu$ m                                                                                                                                                                                                       |
| Fiber Cable Size             | 3mm or 900 $\mu$ m                                                                                                                                                                                                     |
| Fiber Cable Type             | Tight-buffered only                                                                                                                                                                                                    |
| Fiber Type                   | Multimode                                                                                                                                                                                                              |
| Termination Style            | Pre-Polished Crimp                                                                                                                                                                                                     |
| Ferrule Type                 | Zirconia Ceramic                                                                                                                                                                                                       |
| No. of Module Spaces         | 1                                                                                                                                                                                                                      |
| Pricing Description          | FJ Crimp Jack Module 62.5 $\mu$ m for 3mm Jacketed Cable or 900 $\mu$ m Buffered Fiber AW                                                                                                                              |
| Min. Order UOM               | PC                                                                                                                                                                                                                     |
| Min. Order Qty.              | 1                                                                                                                                                                                                                      |
| BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>                                                                                                                                                                                         |
| Add to Favorite Product List |                                                                                                                                                                                                                        |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.