



# BITS AND NUT SETTERS

AIMCO has assembled the most complete package of commonly used screwdriver bits and nut setters in the industry. Our goal is to supply you with the highest quality bits and nut setters for all your fastener needs. If you're in the electronics, aerospace or general industry, AIMCO has the bits and nut setters to fit your needs.



Most items are available in both American and Japanese industrial standards to properly fit your fasteners.



Made to order specials are available upon request.

# PHILLIPS® POWER BITS


Puntas Phillips®



| Part No.  | Point<br>Size | mm  | Length |        |
|-----------|---------------|-----|--------|--------|
|           |               |     |        | in     |
| A3S0-2    | 0             | 50  |        | 1.969  |
| A3S1-2    | 1             | 50  |        | 1.969  |
| A3S1-2.75 | 1             | 70  |        | 2.756  |
| A3S1-3    | 1             | 75  |        | 2.953  |
| A3S1-3.5  | 1             | 90  |        | 3.543  |
| A3S1-4    | 1             | 100 |        | 3.938  |
| A3S1-6    | 1             | 150 |        | 5.906  |
| A3S2-1.2  | 2             | 30  |        | 1.181  |
| A3S2-1.6  | 2             | 40  |        | 1.574  |
| A3S2-2    | 2             | 50  |        | 1.969  |
| A3S2-2.75 | 2             | 70  |        | 2.756  |
| A3S2-3    | 2             | 75  |        | 2.953  |
| A3S2-3.5  | 2             | 90  |        | 3.543  |
| A3S2-4    | 2             | 100 |        | 3.938  |
| A3S2-4.7  | 2             | 120 |        | 4.724  |
| A3S2-4.75 | 2             | 125 |        | 4.921  |
| A3S2-6    | 2             | 150 |        | 5.906  |
| A3S2-8    | 2             | 200 |        | 7.874  |
| A3S2-10   | 2             | 250 |        | 9.842  |
| A3S2-12   | 2             | 300 |        | 11.811 |
| A3S3-2    | 3             | 50  |        | 1.969  |
| A3S3-2.75 | 3             | 70  |        | 2.756  |
| A3S3-3    | 3             | 75  |        | 2.953  |
| A3S3-3.5  | 3             | 90  |        | 3.543  |
| A3S3-4    | 3             | 100 |        | 3.938  |
| A3S3-4.7  | 3             | 120 |        | 4.724  |
| A3S3-6    | 3             | 150 |        | 5.906  |
| A3S3-8    | 3             | 200 |        | 7.874  |
| A3S3-10   | 3             | 250 |        | 9.842  |
| A3S3-12   | 3             | 300 |        | 11.811 |


# SLOTTED POWER BITS

Puntas Agujereadas



| Part No.   | Screw<br>Size | Length |       | Blade<br>Thickness | Blade<br>Width |
|------------|---------------|--------|-------|--------------------|----------------|
|            |               | mm     | in    |                    |                |
| A3M8-2     | 8             | 50     | 1.969 | .042               | 0.275          |
| A3M8-2.75  | 8             | 70     | 2.756 | .042               | 0.275          |
| A3M8-3     | 8             | 75     | 2.953 | .042               | 0.275          |
| A3M10-2    | 10            | 50     | 1.969 | .046               | 0.312          |
| A3M10-2.75 | 10            | 70     | 2.756 | .046               | 0.312          |
| A3M10-3    | 10            | 75     | 2.953 | .046               | 0.312          |
| A3M12-2    | 12            | 50     | 1.969 | .050               | 0.360          |
| A3M12-2.75 | 12            | 70     | 2.756 | .050               | 0.360          |
| A3M12-3    | 12            | 75     | 2.953 | .050               | 0.360          |




Reduced Diameter  
Puntas Ranurados Con Diametro  
Reducido



| Part No.   | Screw<br>Size | Length |       | Blade<br>Thickness | Blade<br>Width |
|------------|---------------|--------|-------|--------------------|----------------|
|            |               | mm     | in    |                    |                |
| A3MT1-2    | 1             | 50     | 1.969 | .022               | 0.122          |
| A3MT1-3    | 1             | 75     | 2.953 | .022               | 0.122          |
| A3MT3-2    | 3             | 50     | 1.969 | .030               | 0.154          |
| A3MT3-3    | 3             | 75     | 2.953 | .030               | 0.154          |
| A3MT4-2    | 4             | 50     | 1.969 | .034               | 0.188          |
| A3MT4-2.75 | 4             | 70     | 2.756 | .034               | 0.188          |
| A3MT4-3    | 4             | 75     | 2.953 | .034               | 0.188          |
| A3MT5-2    | 5             | 50     | 1.969 | .036               | 0.250          |
| A3MT5-2.75 | 5             | 70     | 2.756 | .036               | 0.250          |
| A3MT5-3    | 5             | 75     | 2.953 | .036               | 0.250          |
| A3MT6-2    | 6             | 50     | 1.969 | .038               | 0.250          |
| A3MT6-2.75 | 6             | 70     | 2.756 | .038               | 0.250          |
| A3MT6-3    | 6             | 75     | 2.953 | .038               | 0.250          |

# SLOTTED INSERT BITS


Insertos Ranurados



| Part No.   | Screw<br>Size | Length |       | Blade<br>Thickness | Blade<br>Width |
|------------|---------------|--------|-------|--------------------|----------------|
|            |               | mm     | in    |                    |                |
| A38M2-1    | 2             | 25     | 0.984 | 0.026              | 0.281          |
| A38M2-1.5  | 2             | 38     | 1.496 | 0.026              | 0.138          |
| A38M3-1    | 3             | 25     | 0.984 | 0.030              | 0.154          |
| A38M3-1.5  | 3             | 38     | 1.496 | 0.030              | 0.154          |
| A38M4-1    | 4             | 25     | 0.984 | 0.030              | 0.170          |
| A38M4-1.5  | 4             | 38     | 1.496 | 0.034              | 0.188          |
| A38M5-1    | 5             | 25     | 0.984 | 0.036              | 0.219          |
| A38M6-1    | 6             | 25     | 0.984 | 0.040              | 0.219          |
| A38M6-1.5  | 6             | 38     | 1.496 | 0.040              | 0.218          |
| A38M8-1    | 8             | 25     | 0.984 | 0.042              | 0.250          |
| A38M8-1.5  | 8             | 38     | 1.496 | 0.042              | 0.250          |
| A38M10-1   | 10            | 25     | 0.984 | 0.046              | 0.281          |
| A38M10-1.5 | 10            | 38     | 1.496 | 0.046              | 0.281          |
| A38M12-1.5 | 12            | 38     | 1.496 | 0.050              | 0.297          |
| A38M14-1.5 | 14            | 38     | 1.496 | 0.550              | 0.344          |

# TORX® POWER BITS



Puntas Torx®



| Part No.   | Torx<br>Size | Length |       |
|------------|--------------|--------|-------|
|            |              | mm     | in    |
| A3T6-2     | T6           | 50     | 1.969 |
| A3T7-2     | T7           | 50     | 1.969 |
| A3T7-2.75  | T7           | 70     | 2.756 |
| A3T7-3.5   | T7           | 90     | 3.543 |
| A3T7-6     | T7           | 150    | 5.906 |
| A3T8-2     | T8           | 50     | 1.969 |
| A3T8-2.75  | T8           | 70     | 2.756 |
| A3T8-3.5   | T8           | 90     | 3.543 |
| A3T8-6     | T8           | 150    | 5.906 |
| A3T9-2     | T9           | 50     | 1.969 |
| A3T9-2.75  | T9           | 70     | 2.756 |
| A3T9-3.5   | T9           | 90     | 3.543 |
| A3T9-6     | T9           | 150    | 5.906 |
| A3T10-2    | T10          | 50     | 1.969 |
| A3T10-2.75 | T10          | 70     | 2.756 |
| A3T10-3.5  | T10          | 90     | 3.543 |
| A3T10-6    | T10          | 150    | 5.906 |

# TORX® POWER BITS


Puntas Torx®



| Part No.   | Torx<br>Size | Length |       |
|------------|--------------|--------|-------|
|            |              | mm     | in    |
| A3T15-2    | T15          | 50     | 1.969 |
| A3T15-2.75 | T15          | 70     | 2.756 |
| A3T15-3.5  | T15          | 90     | 3.543 |
| A3T15-6    | T15          | 150    | 5.906 |
| A3T20-2    | T20          | 50     | 1.969 |
| A3T20-2.75 | T20          | 70     | 2.756 |
| A3T20-3.5  | T20          | 90     | 3.543 |
| A3T20-6    | T20          | 150    | 5.906 |
| A3T25-2    | T25          | 50     | 1.969 |
| A3T25-2.75 | T25          | 70     | 2.756 |
| A3T25-3.5  | T25          | 90     | 3.543 |
| A3T25-6    | T25          | 150    | 5.906 |
| A3T27-2    | T27          | 50     | 1.969 |
| A3T27-2.75 | T27          | 70     | 2.756 |
| A3T27-3.5  | T27          | 90     | 3.543 |
| A3T27-6    | T27          | 150    | 5.906 |
| A3T30-2    | T30          | 50     | 1.969 |
| A3T30-2.75 | T30          | 70     | 2.756 |
| A3T30-3.5  | T30          | 90     | 3.543 |
| A3T30-6    | T30          | 150    | 5.906 |
| A3T40-2    | T40          | 50     | 1.969 |
| A3T40-2.75 | T40          | 70     | 2.756 |
| A3T40-3.5  | T40          | 90     | 3.543 |
| A3T40-6    | T40          | 150    | 5.906 |

## TAMPER RESISTANT

Torx® (Extra Resistencia)



| Part No.  | Torx<br>Size | Length |       |
|-----------|--------------|--------|-------|
|           |              | mm     | in    |
| A3T10-2TR | T10          | 50     | 1.969 |
| A3T15-2TR | T15          | 50     | 1.969 |
| A3T20-2TR | T20          | 50     | 1.969 |
| A3T25-2TR | T25          | 50     | 1.969 |