





Materials and Finish

Shell: Steel, Tin plated

Contacts: Phosphor Bronze,
20-30u" Nickel underplated
W/ 20-30u" Silver Finish

Insulation: PBT, black
UL94V-0 rated

Electrical Characteristics

Rating: 100v AC (rms) 1amp Max.
12v DC 2amp Max.

Insulation Resistance:
50 Megohm Min. at 250v DC

Dielectric Strength:
250v AC for 1 minute

Contact Resistance:
30 milliohm Max.

Operating Temperature:
-25°C to +80°C

CSA NRTL/C Certified File No. LR78160

REVISION	DATE	DESCRIPTION	DRAWN BY	DESIGNED BY	UNITS	KMDP-6S-M	6 pos. Panel Mount Female Mini-DIN	
B1	4/7/99	Edit Dims	J. Kring		mm			
B2	3/29/00	Ref ECD 00-080	CHECKED BY	APPROVED BY	DATE			
B3	4/19/01	ECD 01-062	M. Yiu		1/21/97		Metal Shell	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KMDP-6S-M](#)