

REV.	DESCRIPTION	DATE
A	RELEASE	2012/11/7

NUMBER OF POSITIONS	DIMENSION	
	A	B
08	7.62	14.86
10	10.16	17.40
12	12.70	19.94
14	15.24	22.48
16	17.78	25.02
18	20.32	27.56
20	22.86	30.10
22	25.40	32.64
24	27.94	35.18
26	30.48	37.72
28	33.02	40.26
30	35.56	42.80
34	40.64	47.88
36	43.18	50.42
40	48.26	55.50
44	53.34	60.58
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating:flash gold

Contact Material: Brass












Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.


Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



14P-64P



UNLESS TOLERANCE		DRAW	BY	CnC Tech,LLC	
GENERAL	ANGLE	DESIGN	BY		
X. ± 0.30	X.° ± 3.0°	CHECK	BY	Port NO. 3030-XX-0104-00	
.X ± 0.25	.X° ± 2.0°	APPROVE	BY		
.XX ± 0.20	.XX° ± 1.0°	SCALE		SHEET	
.XXX ± 0.10	.XXX° ± 0.5°				
SCALE		1:1	1/1	UNIT	
DRAW NO:		MM		REV: A	